### **SkyTrim** Decorative Accent for SkyRidge

# **Metalux**







Designed for an array of interior applications, **SkyTrim**<sup>™</sup> is a luminous decorative accent that can be mounted directly on the light guide of a SkyRidge<sup>™</sup> fixture. A co-extruded high-grade optical acrylic strip, less than 0.5" deep, the SkyTrim provides a simple means of applying color to an existing or new fixture. It is ideal for spaces where color is necessary to provide visual cues, emphasize brand identity, directional awareness or simply as an artistic expression. The result is a unique and easy accessory for addressing a wealth of application needs with seven color choices and hundreds more with custom color options.

#### **Features and Benefits**

- Flexible use of color for identification, awareness or artistic purpose in space
- Seven standard color choices with custom color options



- Offered in both 2' and 4' lengths
- Factory or field installable
- Simple installation; no hardware or tools required
- High-grade optical acrylic
- Minimal 0.45" depth

### **Suggested Applications**

- Healthcare: wayfinding, paths of egress
- Education: school colors, space identification, pathways
- Sport Venues: team colors, zone/activity identification
- Retail: highlight merchandise, traffic influencer, customer checkout/service area identification
- Corporate Facilities: department identifiers, campus coding, branding, awareness
- Hospitality / Event: color coordination by activity, customer colors or holidays

# **Ordering Information** (with fixture)

Sample Number: 22SR-LD2-29-C-UNV-L835-CD1-SVPD1-U


Rating	Series	Air	Lamp Type	LE	D Lumens Out	put					Reflector
[Blank]=Standard ATW-SW4=Chicago Rated <sup>7</sup>	22SR=2' × 2' SkyRidge 24SR=2' × 4' SkyRidge 14SR=1' × 4' SkyRidge 12SR=1' × 2' SkyRidge	[Blank]=Standard A=Air Vented <sup>6, 15</sup>	LD2=LED 2.0	29 MT	eck =2000 Lumens =2900 Lumens	2' x 4' Stock 39=3900 Lu 48=4800 Lu MTO <sup>2</sup> 29=2900 Lu 34=3400 Lu 45=4500 Lu 53=5300 Lu 64=6400 Lu	imens imens imens imens imens imens imens	1' x 4' MTO <sup>2</sup> 15=1500 Lumens 20=2000 Lumens 25=2500 Lumens 30=3000 Lumens 35=3500 Lumens 40=4000 Lumens 45=4500 Lumens	1' x 2' MTO <sup>2</sup> 9=900 Lur 12=1200 L 16=1600 L 20=2000 L	umens umens	C=Curved (Standard) S=Straight
Optics	Voltage <sup>3</sup>	Options			ССТ	Options		Driver Type⁵			Number of Drivers
[Blank]=Standard	347V=347 Volt UNV=Universal Voltage 120-277	Emergency EL7W=7-watt, 120' battery pack installe EL14W=14-watt 12 battery pack installe GTD2=Bodine Gen ETS2=IOTA Emerg	ed <sup>17</sup> 0V-277V emergen ed <sup>17</sup> erator Transfer De	cy vice <sup>19</sup>	CCT L830=3000K L835=3500K L840=4000K L850=5000K	Flex <sup>4</sup> Flex=Multip Config Availab	urations	SD=Step-Dim Drive HCD=0-10V Dimmi 100% Dimmi 5LTD=Fifth Light D. 100% Dimmi 5LTHD=Fifth Light	CD=0-10V Dimming Driver (Standard)   1     SD=Step-Dim Driver <sup>1,14</sup> 2     HCD=0-10V Dimming Driver (1% - 100% Dimming) <sup>18</sup> 2     5LTD=Fifth Light DALL Driver (10% - 100% Dimming) <sup>6,13</sup> 1     5LTHD=Fifth Light DALL Driver (1% - 100% Dimming) <sup>5,12</sup> 1		
Product Family	Control	Туре		Occupancy Technology Sensing Technology Cover		age Pattern					
		r Mounting, No Sens g (0-10V) Output for I	ng, No Sensor Output for Local Control <sup>16</sup>		P=Passive Infrared D			Dimming Daylight Harvesting (Closed Loop)		1=~144 Square Feet	
SkyTrim <sup>10</sup>		Packagir	g	Acce	essories (Orde	Separately	7)				
TB=Tahitian Blue PG=Primary Green SO=Storaro Orange PL=Pearl				T3A END E.O. BRACKET PARTS BAG= (Standard with Fixture) DF-14-W=1' x 4' Drywall Fra DF-22-W=2' x 2' Drywall Fra DF-22-W=2' x 2' Drywall Fra DF-24-W=2' x 4' Drywall Fra DF-24-W=2' x 4' Drywall Fra SK-22-WT=2' x 2' Surface M SK-22-WT=2' x 4' Surface M SK-24-WT=2' x 4' Surface M					ame Kit ame Kit Aount Kit, Tall		

NOTES: 1. 1' x 2' is not available with Step-dim or Fifth Light drivers. 2. Made-to-order (MTO) requires four week lead time. 3. Products also available in non-US voltage and frequencies for international markets. 4. Flex does not include dimming leads. Control leads provided by others. 5. For a complete listing of Fifth Light products, visit www.eaton.com/lightingsystems. 6. Air version is vented but does not meet air handling requirements. Air version is non-IC. Air version is not available with integrated sensor. **Z** Chicago rated version does not allow for row mounting. **9**. Must be used in conjunction with a DALI control system. For complete DALI solutions by Fifth Light, visit www.coopercontrol.com. **10**. Fixtures using factory installed SkyTrim option do not meet DLC qualifications. **11**. Custom colors must list Roscolux numeric color specification code. **12**. 5LTHD option uses two drivers at 6400 lumens. **13**. 5LTD option is not available in 1' x 4': 1500, 2000, 2500, 3000 and 3500, 2' x 2': 3000 and 3500 lumen packages. **14**. 2' x 2': 2900 and 3400, 1' x 4': 1500, 2000, 2500, 3000 and 3500 lumen packages are not available with Step-dim driver. **15.** Air vented version not available with 1' x 4': and 1' x 2'. **16.** Integral sensor works only with "CD" driver and is factory prewired to the driver for stand-alone control. **17.** With integral test switch/indicator/laser test. For approximate delivered lumens multiply the lumens per watt of the desired fixture by the wattage of the emergency battery pack (100 lm/W x 7=700 lumens). IES-format photometry for luminaire under emergency operation available. 18. HCD driver option is not available with 1' x 4': 1500 lumen package. 19. Used to transfer fix ture to secondary power source for life-safety operation. When used with a dimming fix ture, two devices are required to ensure control is disabled while operating under emergency power

Specifications & dimensions subject to change without notice. Consult your Eaton Representative for availability and ordering information.

## **Field Installed Ordering Information**

Color Choice	2' Kit Catalog Number	4' Kit Catalog Number	Kit Quantity
Tahitian Blue	STK-2-TB-10PK	STK-4-TB-10PK	10
Primary Green	STK-2-PG-10PK	STK-4-PG-10PK	10
Storaro Orange	STK-2-SO-10PK	STK-4-SO-10PK	10
Pearl	STK-2-PL-10PK	STK-4-PL-10PK	10
Belladonna Rose	STK-2-BR-10PK	STK-4-BR-10PK	10
Medium Red	STK-2-MR-10PK	STK-4-MR-10PK	10
Straw	STK-2-ST-10PK	STK-4-ST-10PK	10
Custom Color	STK-2-CC-*-10PK	STK-4-CC-*-10PK	10



\* Custom color requires Roscolux numeric specification color code. NOTE: Chosen color will be matched on acrylic but will appear lighter once applied to lit light guide.



2

Our Lighting

Product Lines Halo Halo Commercial Portfolio Iris RSA Metalux Corelite Neo-Ray Fail-Safe MWS Ametrix Shaper io Lumark McGraw-Edison Invue Lumière Streetworks AtLite Sure-Lites

#### Our Controls Product Lines

Greengate iLumin Zero 88 Fifth Light Technology iLight (International Only)

1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.eaton.com/lighting Canada Sales

Eaton

Canada Sales 5925 McLaughlin Road Mississauga, Ontario L5R 1B8 P: 905-501-3000 F: 905-501-3172 © 2016 Eaton All Rights Reserved Printed in USA Publication No. ADF141479 February 12, 2016 Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.

