

Watertight NEMA 4X Locking Plug

24W47



Locking Watertight Plug 15amp 125volt
L5-15p



features & benefits

- Rubber body construction stands up to impacts, oil, chemicals, heat, and weather.
- Floating blades allow self-alignment with contacts and reduce stress on blades and contacts.
- Neoprene grommet keeps out contaminants at cord entrance.
- Terminal screws come backed out -- ready-to-wire.
- Nickel-plated blades and connectors provide an extra measure of corrosion resistance.
- Closure cap on watertight model forms a seal to keep out contaminants when connector is not in use.
- Multiple seals between plug and connector on watertight version protects electrical connection from contaminants.

specifications

General Info

Type: Plug
Number Of Wires: 3
Special Features: Watertight, NEMA

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 42M
CSA Standard: Yes
UL Listing No: 498
UL Standard: Yes

UN SPS C: 39121403

Dimensions

Diameter U S: 1.560"

Length U S: 2.630"

Technical Information

Amps: 15 Amp

Material: Rubber

NEMA Configuration Number: L5-15P

Volts: 125V

Volts A C: 125

Buy American Act Compliance

Country of Origin: UNITED-STATES-OF-AMERICA

Buy American Act Status: Trade Agreement Act Compliant