## IC-Rated 600 Lumen Downlights, Gen 4

Refined, ultra-efficient, high-performance illumination for residential, retail and commercial applications





# Juno<sup>®</sup> IC-Rated 600 Lumen LED Downlights, Gen 4

#### Featuring improved 90 CRI color rendering

The Generation 4 line of recessed LED downlights is just what you'd expect from Juno. It's the most all-inclusive LED downlight lineage, including 4", 5", and 6" apertures with higher performance, better color rendering and new hyperbolic trims. Juno Generation 4 Recessed LED downlights are ENERGY STAR® certified and are compliant with the latest California Title 24 energy code.

## Juno 4" IC-Rated 600 Lumen Generation 4 LED Downlights

#### 4" New Construction



Shown with universal voltage driver.

121/4" L x 63/4" W x 6" H Ceiling cutout: 41/2"

#### IC1LED & IC1RLED G4 Series

Dedicated 4" LED new construction and remodel housings with integral light engine and choice of dimmable drivers. The eldoLED driver option delivers smooth and flicker-free deep dimming performance. Shallow housing construction allows for fit in 2 x 6 construction. Air-Loc® gasket kit (Remodel only) supplied with housing. IC housing designed for use with IC or non-IC construction. Wide flood optic provided as standard. Also available with WarmDim® technology.

#### 4" Remodel



Shown with dedicated 120 volt driver.

141/8" L x 43/4" W x 43/8" H Ceiling cutout: 43/8"

Example: IC1LED G4 06LM 27K 90CRI 120 FRPC

Series	Gen	Lumens	CCT	CRI	Voltage/Driver
IC1LED 4" New Construction Housing	G4	06LM 600 Lumens	27K 2700K 30K 3000K 35K 3500K 40K 4000K	<b>90CRI</b> 90 CRI	120 FRPC 120V Only; Forward Phase/ ELV Dimming
IC1RLED 4" Remodel Housing					Universal 120-277V; 0-10V Dimming
					MVOLT EZ1* Multi-Volt (120-277V) eldoLED 0-10V, 1% dim

\*A+ Capable



A+ Capable configurations support A+ Certified Solutions. A+ Certified solutions from Acuity Brands help you quickly and confidently select and implement lighting systems that are both compatible and consistent. Go to www.acuitybrands.com/APlus or contact your local Acuity Brands representative for more information.

#### **4" LED Downlight Trims**

#### **Downlights**



Pinhole with Integral Shield 13 WH

2" Aperture



#### Baffle

- 14 BWH Black
- 14 BSC Black 14 BABZ Black
- 14 BBL Black
- 14 WWH White

33/8" Aperture



#### Cone

- 17 CWH Clear Alzak<sup>®</sup> 17 GWH Gold Alzak<sup>®</sup> 17 BWH Black Alzak<sup>®</sup>
- 17 PTSC Pewter Alzak®
  17 WWH Gloss White
- 17 HZWH Haze 17 WHZWH Wheat Haze
- 17 WHZABZ Wheat Haze 33/8" Aperture

#### **Decorative**



Beveled Cylinder 4103 FROSTWH 4103 FROSTSC 3" Aperture



Beveled Cone 4104 HZSC Haze 4104 WHZABZ Wheat Haze

33/8" Aperture



Glass Cylinder 4150 MESHSC

**Hyperbolic** 

25/8" Aperture



17HYP2 CWH Clear Alzak®
17HYP2 BWH Black Alzak®
17HYP2 WWH White
17HYP2 HWWH Haze
17HYP2 WHZWH Wheat Haze
17HYP2 WHZABZ Wheat Haze

#### Lensed



#### Wall Wash

**39 CWH** Clear Alzak® **39 HZWH** Haze **39 WWH** Gloss White **39 WHZWH** Wheat Haze



Wet Location

Drop Opal 11 WH





Frosted Lens with Clear Center 12 WWH

12 WWH 12 WSC 12 WABZ



Beveled Dome -Lensed 4101 ABZ 4101 SC

4101 WH





9



#### **Square Trims**



13SQ WH White Trim



17SQ HZWH Haze, White Trim 17SQ WWH White, White Trim 17SQ BWH Black, White Trim 17SQ WHZWH Wheat Haze



Frosted Lens with Clear Center 12SQ WWH White Trim

### Juno 5" IC-Rated 600 Lumen Generation 4 LED Downlights

IC20LED & IC20RLED G4 Series

Dedicated 5" LED new construction

and remodel housings with integral

light engine and choice of dimmable

delivers smooth and flicker-free deep

dimming performance. Shallow housing construction allows for fit in 2 x 6

construction. Air-Loc gasket kit (Remodel

only) supplied with housing. IC housing

designed for use with IC or non-IC

provided as standard. Also available

construction. Wide flood optic

with WarmDim® technology.

drivers. The eldoLED driver option

#### **5" New Construction**



Shown with universal

15¾" L x 91/8" W x 47/8" H Ceiling cutout: 5%"

#### 5" Remodel



Shown with dedicated 120 volt driver.

13½" L x 5¾" W x 4¾" H Ceiling cutout: 51/2"

Example: IC20LED G4 06LM 27K 90CRI 120 FRPC

Series	Gen	Lumens	CCT	CRI	Voltage/Driver
IC20LED 5" New Construction Housing IC20RLED 5" Remodel Housing	G4	06LM 600 Lumens	27K 2700K 30K 3000K 35K 3500K 40K 4000K	<b>90CRI</b> 90 CRI	120 FRPC 120V Only; Forward Phase/ ELV Dimming  MVOLT ZT Universal 120-277V; 0-10V Dimming
					MVOLT EZ1* Multi-Volt (120-277V) eldoLED 0-10V, 1% dim

\*A+ Capable

Refer to the specification sheet for the list of factory qualified dimmer model numbers.

Note: ENERGY STAR® and T24 certification is dependent on trim finish and LED color temperature. See housing spec sheet for specific information for each trim.

\*\*Do not use reflector shipped with trim for LED housing. Discard or recycle reflector.



A+ Capable configurations support A+ Certified Solutions. A+ Certified solutions from Acuity Brands help you quickly and confidently select and implement lighting systems that are both compatible and consistent. Go to www.acuitybrands.com/APlus or contact your local Acuity Brands representative for more information.

#### **5" LED Downlight Trims**

#### **Downlights**





**Downlight Baffle** 205 WWH White 205 BWH Black 205 BSC Black 205 BABZ Black

43/8" Aperture





#### **Downlight Cone**

204 CWH Clear Alzak® 204 GWH Gold Alzak® 204 BWH Black Alzak® 204 PTSC Pewter Alzak® 204 WWH Gloss White **204 HZWH** Haze **204 WHZWH** Wheat Haze 204 WHZABZ Wheat Haze

43/8" Aperture

#### **Wall Wash**



213G3 WWH White 213G3 BWH Black

#### **Hyperbolic**



204HYP2 CWH Clear Alzak® 204HYP2 BWH Black Alzak® 204HYP2 WWH White 204HYP2 HZWH Haze 204HYP2 WHZWH Wheat Haze 204HYP2 WHZABZ Wheat Haze

#### Lensed





Flat Glass Shower Trim\*\* **210N ABZ** 210N SC 210N WH





Frosted Lens with Clear Center\*\* 212N ABZ 212N SC 212N WH





White Baffle, **Regressed Frosted** Dome Lens\*\* 2130 WWH White 2130 BWH Black





Beveled Frame, Frosted Dome Lens\*\* 5101 ABZ 5101 SC 5101 WH

## Juno 6" IC-Rated 600 Lumen Generation 4 LED Downlights

#### **6" New Construction**



Shown with universal voltage driver.

15¾" L x 91/8" W x 47/8" H Ceiling cutout: 67/8"

#### IC22LED & IC22RLED G4 Series

Dedicated 6" LED new construction and remodel housings with integral light engine and choice of dimmable drivers. The eldoLED driver option delivers smooth and flicker-free deep dimming performance. Shallow housing construction allows for fit in 2 x 6 construction. Air-Loc® gasket kit (Remodel only) supplied with housing. IC housing designed for use with IC or non-IC construction. Wide flood optic provided as standard. Also available with WarmDim® technology.

#### 6" Remodel



Shown with dedicated 120 volt driver.

14½" L x 7¼" W x 51/8" H Ceiling cutout: 63/4"

#### Example: IC22LED G4 06LM 27K 90CRI 120 FRPC

Series	Gen	Lumens	CCT	CRI	Voltage/Driver
IC22LED 6" New Construction Housing IC22RLED 6" Remodel	G4	<b>06LM</b> 600 Lumens	27K 2700K 30K 3000K 35K 3500K 40K 4000K	<b>90CRI</b> 90 CRI	120 FRPC 120V Only; Forward Phase/ ELV Dimming  MVOLT ZT Universal 120-277V; 0-10V Dimming
Housing					MVOLT EZ1* Multi-Volt (120-277V) eldoLED 0-10V, 1% dim

<sup>\*</sup>A+ Capable

Refer to the specification sheet for the list of factory qualified dimmer model numbers.

Note: ENERGY STAR® and T24 certification is dependent on trim finish and LED color temperature. See housing spec sheet for specific information for each trim.

\*\*Do not use reflector shipped with trim for LED housing. Discard or recycle reflector.



A+ Capable configurations support A+ Certified Solutions. A+ Certified solutions from Acuity Brands help you quickly and confidently select and implement lighting systems that are both compatible and consistent. Go to www.acuitybrands.com/APlus or contact your local Acuity Brands representative for more information.

#### Photo Credits:

Cover: Private Residence, St. Charles, IL (Pictureboy Photography)

#### **6" LED Downlight Trims**

#### **Downlights**





#### **Downlight Baffle**

24 WWH White 24 BWH Black 24 BSC Black

24 BABZ Black 24 BBL Black

53/4" Aperture





#### **Downlight Cone**

27 CWH Clear Alzak® 27 GWH Gold Alzak®

27 BWH Black Alzak® 27 PTSC Pewter Alzak®

27 WWH Gloss White

27 HZWH Haze 27 WHZWH Wheat Haze 27 WHZABZ Wheat Haze

53/4" Aperture

#### **Decorative**



**Octagonal** 9024 WWH 5¾" Aperture



**Luminous Disc (Frosted)** 9324 SC

31/4" Aperture



**Metal Band** 9524 SC

51/8" Aperture



**Luminous Collar (Frosted)** 9702

63/8" Aperture

#### **Wall Wash**



Wall Wash 262G3 WWH White 262G3 BWH Black

#### Lensed





**Albalite** 

20 PW Shower/Closet Light 20 WH











Fresnel 22 WH





Frosted Lens\*\* 239 WH





Frosted Lens with **Clear Center 242 ABZ** 242 SC 242 WH





**Decorative Swirled Etched Opal Glass\*\*** 243 WH







2330 BWH Black





Beveled Frame, Frosted Dome Lens\*\* 6101 ABZ

6101 SC 6101 WH

#### **Hyperbolic**



27HYP2 CWH Clear Alzak® 27HYP2 BWH Black Alzak® 27HYP2 WWH White 27HYP2 HZWH Haze 27HYP2 WHZWH Wheat Haze 27HYP2 WHZABZ Wheat Haze



All trademarks referenced are property of their respective owners. Specifications subject to change without notice. Printed in the U.S.A.