



**Product Number:** 14664

**Order Abbreviation:** 250BR40/1 120V

**General Description:** Incandescent BR40 Infrared Reflector Lamp Clear Finish Medium Brass Base 250Watt 120Volt Retail Pack

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	250BR401 120V 6/CS 1/SKU
Approx. Lumens	2000
Average Rated Life (hr)	5000
Base	Medium Brass
Bulb	BR40
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	5.000
Diameter (mm)	127.00
Filament	CC-6
Lamp Finish	Reflector IR
Maximum Overall Length - MOL (in)	6.500
Maximum Overall Length - MOL (mm)	165.1
Nominal Voltage (V)	120.00
Nominal Wattage (W)	250.00



#### Footnotes

- Designed for service other than illumination.
- Operate only in porcelain sockets.
- Should be shielded against moisture falling on bulb.
- May not give satisfactory performance if any accessory lighting equipment touches the glass bulb.