



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



250SRTI 1/2" Ins Steel Emt Raintight Compression Conn

Nsi Industries

Catalog Number	250SRTI
Manufacturer	Nsi Industries
Description	Compression Connector, 1/2 In Trade Size, Straight Connection Orientation, Zinc Electro-Plated, Insulated, 1-3/4 In Length, 1-1/32 In Diameter, +105 °C Operating Temperature, 0.0006 LB/Ea
Weight per unit	0.0006 (lbs/each)
Product Category	Steel Insulated Straight Compr

Features

Connector Type	Steel Raintight/Concrete-Tight Insulated
insulation	Insulated Throat
media	Yes

Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

Dimensions and Weight

Size	1/2
------	-----

Descriptions

Description	1/2" INS STEEL EMT RAIN TIGHT COMPRESSION CONN
extra long description	BPT 250-SRTI 1/2 IN Steel Raintight

Manufacturer Information

Brand	Bridgeport
GTIN	00781747122506
UPC	781747122506

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	CONNECTOR

Packaging

Carton	25
Package	250
Weight Per each	0.0006

Uses, Certifications, and Standards

Application	Used to join EMT to box or enclosure. Concrete tight/Raintight. Insulated Throat - 105°C. Patented
standard	cULus