

## 6" Deluxe Universal Housings



### IC Housing

Energy-efficient, Air-Loc® double wall housing can be covered with insulation.

**IC2** with Real Nail® 3 bar hangers  
**IC2W** with push-in electrical connectors and Real Nail® 3 bar hangers

17 $\frac{1}{8}$ " L x 9 $\frac{1}{8}$ " W x 7 $\frac{1}{2}$ " H  
 Ceiling cutout: 6 $\frac{1}{8}$ "



### TC Housing

Requires 3" spacing from insulation.

**TC2** with Real Nail® 3 bar hangers  
**TC2S** with smaller footprint bar hanger (Real Nail® 2)  
**TC2W** with push-in electrical connectors and Real Nail® 3 bar hangers

13 $\frac{1}{8}$ " L x 7 $\frac{1}{2}$ " W x 7 $\frac{1}{2}$ " H  
 Ceiling cutout: 6 $\frac{1}{8}$ "



### TC Remodel Housing

Requires 3" spacing from insulation. Installs from below ceiling.

**TC2R** Remodel Housing

13 $\frac{3}{4}$ " L x 7 $\frac{1}{8}$ " W x 5 $\frac{1}{4}$ " min H;  
 7 $\frac{1}{4}$ " max H  
 Ceiling cutout: 6 $\frac{3}{4}$ "

**Note:** In Canada when insulation is present, Type IC fixtures must be used.

## 6" Deluxe Universal Trims

### Downlights




**Tapered Baffle**†  
**24W-WH** White  
**24B-BL** Black  
**24B-WH** Black  
**24B-ABZ** Black  
**24B-SC** Black  
 75W PAR30L,  
 65W BR30  
 5 $\frac{1}{4}$ " Aperture



**Straight Baffle**†  
**25W-WH** White  
**25B-WH** Black  
**25B-BL** Black  
**25B-SC** Black  
 IC: 85W BR40, 90W PAR38  
 TC: 150W PAR38, 120W  
 BR40  
 5 $\frac{1}{4}$ " Aperture



**PAR30 Deep Cone**†  
**257B-WH** Black Alzak®  
**257C-WH** Clear Alzak®  
**257G-WH** Gold Alzak®  
**257HZ-WH** Haze  
**257WHZ-WH** Wheat Haze  
 75W PAR30, 100W PAR38  
 5 $\frac{1}{2}$ " Aperture



**BR30 Open Frame**  
**250-ABZ**  
**250-SC**  
**250-WH**  
 65W BR30  
 4" Aperture



**Pinhole with Baffle**  
**23B-WH** Black  
 50W R/PAR20  
 3 $\frac{3}{8}$ " Aperture



**PAR30 Deep Baffle**†  
**254W-WH** White  
**254B-WH** Black  
 75W PAR30, 100W PAR38  
 5 $\frac{1}{2}$ " Aperture



**BR40/R40 Open Frame**  
**251-WH**  
 IC: 100W BR40  
 TC: 120W BR40, 250W R40  
 Heat Lamp  
 5 $\frac{1}{2}$ " Aperture

**More trim selection on the next page** →



**Straight Cone**†  
**26B-WH** Black Alzak®  
**26C-WH** Clear Alzak®  
**26G-WH** Gold Alzak®  
**26HZ-WH** Haze  
**26PT-SC** Pewter Alzak®  
**26W-WH** Gloss White  
**26WHZ-WH** Wheat Haze  
 IC: 90W PAR38, 85W BR40  
 TC: 150W PAR38,  
 120W BR40  
 5 $\frac{1}{4}$ " Aperture



**Tapered Cone**\*†  
**27B-WH** Black Alzak®  
**27C-WH** Clear Alzak®  
**27G-WH** Gold Alzak®  
**27HZ-WH** Haze  
**27PT-SC** Pewter Alzak®  
**27W-WH** Gloss White  
**27WHZ-ABZ** Wheat Haze  
**27WHZ-WH** Wheat Haze  
 75W PAR30L, 65W BR30  
 5 $\frac{1}{2}$ " Aperture

### Accessories

**ALG6:** Energy Conserving Gasket for  
 6" New Construction Air-Loc® IC Housings

\* Trim may be used with TC2R housing adjusted in lowest (5 $\frac{1}{4}$ " ) height position.

† See accessory page 161 for additional trim ring finishes, order separately.

### Trim Ring Finishes

**ABZ:** Classic Aged Bronze  
**SC:** Satin Chrome  
**WH:** White  
**BL:** Black



# 6" Standard Universals

Standard Universal downlights are offered with basic trim options but include all the installation and performance features Juno is known for.

## 6" Standard Universal Housings



**Economy IC Housing**  
Energy-efficient, Air-Loc® housing can be covered with insulation.

- IC22** with Real Nail® 3 bar hangers
- IC22S** with smaller footprint bar hanger (Real Nail® 2)
- IC22W** with Real Nail® 3 bar hangers and quick electrical connectors.

13 1/8" L x 7 1/2" W x 7 1/8" H  
Ceiling cutout: 6 3/4"



**Economy IC Remodel Housing**  
Energy-efficient, Air-Loc® housing can be covered with insulation. Installs from below ceiling with clips provided.

**IC22R** Remodel Housing  
13 3/4" L x 7 7/16" W x 7 1/8" H  
Ceiling cutout: 6 3/4"

## 6" Standard Universal Trims

### BR/PAR Downlights




**Tapered Cone†**  
**27B-WH** Black Alzak®  
**27C-WH** Clear Alzak®  
**27G-WH** Gold Alzak®  
**27HZ-WH** Haze  
**27PT-SC** Pewter Alzak®  
**27W-WH** Gloss White  
**27WHZ-ABZ** Wheat Haze  
**27WHZ-WH** Wheat Haze  
 50W PAR30, 65W BR30,  
 75W PAR30L  
 5 3/4" Aperture



**Tapered Baffle†**  
**24W-WH** White  
**24B-WH** Black  
**24B-ABZ** Black  
**24B-BL** Black  
**24B-SC** Black  
 75W PAR30L,  
 50W PAR30, 65W BR30  
 5 3/4" Aperture



**Shallow Baffle†**   
**244W-WH** White  
**244B-WH** Black  
 60W PAR30, 65W BR30,  
 75W PAR30L  
 5 3/4" Aperture



**Straight Baffle†**  
**25W-WH** White  
**25B-BL** Black  
**25B-ABZ** Black  
**25B-WH** Black  
**25B-SC** Black  
 50W PAR30, 65W BR30



**Ultra-Trim Cone - Fully Enclosed\***   
 (Wet Location w/  
 Outdoor Lamps)  
**29C-WH** Clear Cone  
**29W-WH** White Cone  
 60W A19, 65W BR30,  
 75W PAR30/30L,  
 90W PAR38/BR40  
 5 3/4" Aperture



**BR30 Open Frame**  
**250-ABZ**  
**250-SC**  
**250-WH**  
 65W BR30  
 4" Aperture



**Shallow Cone†**   
**247B-WH** Black Alzak®  
**247C-WH** Clear Alzak®  
**247G-WH** Gold Alzak®  
**247HZ-WH** Haze  
**247WHZ-WH** Wheat Haze  
 75W PAR30L, 65W BR30,  
 75W PAR30  
 5 3/4" Aperture



**BR30 Regressed Open Frame**  
**252-WH**  
 65W BR30  
 4" Aperture



**Ultra-Trim Baffle - Fully Enclosed\***   
 (Wet Location w/  
 Outdoor Lamps)  
**28W-WH** White  
**28B-WH** Black  
 60W A19, 65W BR30,  
 75W PAR30/30L,  
 90W PAR38/BR40  
 5 3/4" Aperture

### Adjustables



**Cylinder Spotlight in Baffle**  
**226W-WH** White  
 Cylinder  
 in White Baffle  
**226B-WH** Black  
 Cylinder  
 in Black Baffle  
 60W PAR16

### Adjustables, cont.



**R/PAR20 Regressed Eyeball**  
**228-WH**  
 50W R/PAR20

**R/PAR20 Regressed Eyeball in Baffle**  
**248W-WH** White  
 50W R/PAR20



**PAR/BR30 Regressed Eyeball**  
**229-ABZ**  
**229-BL**  
**229-SC**  
**229-WH**  
 75W PAR30L, 65W BR30

**PAR/BR30 Regressed Eyeball in Baffle**  
**249W-WH** White  
**249B-WH** Black  
 75W PAR30L, 65W BR30