

Bridgeport Fittings Inc.


705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488

Connectors - Zinc

Images





Dimension A in Inches: 7/16 Dimension B in Inches: 15/16 Dimension C in Inches: 1-7/16

Application

Used to join steel EMT to box or enclosure. Concrete-tight. 1/2" thru 2" suitable for use with Steel or Aluminum EMT. Insulator rated 105°C. CSA Listed Raintight/For Use in Wet Locations in Canada Only

Product Information

Material: Zinc Die Cast

Finish: Ball burnished, mirror smooth

Certifications & Codes:

CSA File Number: LR39354
Federal Specification Number: A-A-50553
NEMA Standard: FB-1
UL File Number: E24001
UL Standard: UL-514B
UNSPSC: 39121434

Catalog ID: 251-DCI2

UPC Number: 781747162519

Description: Connector, Compression, Zinc Die Cast,

105°C Insulated Throat, Size 3/4 Inch

Application: Used to join steel EMT to box or enclosure. Concrete-tight. 1/2" thru 2" suitable for use with Steel or Aluminum EMT. Insulator rated 105°C. CSA Listed Raintight/For Use in Wet Locations in Canada Only

Trade Size: 3/4"

Country of Manufacture: USA

Std Pkg Qty: 250

Unit Qty: 25