


Connectors - Zinc - Raintight

Images





Download Photo Image Dimension A in Inches: 7/16 Dimension B in Inches: 15/16 Dimension C in Inches: 1-7/16

Download Dimensional Image

Bridgeport Fittings Inc. 705 Lordship Blvd. Stratford, CT 06615

> Phone: 203-377-5944 Fax: 203-381-3488

Application

Compression style connector with internal sealing ring and knockout gasket to create a raintight seal when connecting EMT to box or enclosure. Insulated Throat -90° C. Patented

Product Information

Material: Zinc Die Cast Finish: Ball burnished, mirror smooth

Certifications & Codes:

Federal Specification Number: A-A-50553 **NEMA Standard:** FB-1 UL File Number: E24001 UL Standard: UL-514B UNSPSC: 39121434

Catalog ID: 251-RTI2

UPC Number: 781747192516

Description: 3/4" Raintight Compression Connector, Insulated

Application: Compression style connector with internal sealing ring and knockout gasket to create a raintight seal when connecting EMT to box or enclosure. Insulated Throat - 90° C. Patented

Trade Size: 3/4"

Std Pkg Qty: 250

Unit Qty: 25