

Bridgeport Fittings Inc.


705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488

Connectors - Zinc - Raintight

Images





Download Photo Image Download Dimensional Image

Dimension A in Inches: 5/8
Dimension B in Inches: 1-3/16
Dimension C in Inches: 2-1/8

Application

Compression style connector with internal sealing ring and knockout gasket to create a raintight seal when connecting EMT to box or enclosure. Insulated Throat - 90° C. Patented

Product Information

Material: Zinc Die Cast

Finish: Ball burnished, mirror smooth

Certifications & Codes:

Federal Specification Number: A-A-50553 NEMA Standard: FB-1 UL File Number: E24001 UL Standard: UL-514B UNSPSC: 39121434

Catalog ID: 253-RTI2

UPC Number: 781747192530

Description: 1-1/4" Raintight Compression Connector,

Insulated

Application: Compression style connector with internal sealing ring and knockout gasket to create a raintight seal when connecting EMT to box or enclosure. Insulated Throat

- 90° C. Patented

Trade Size: 1-1/4"

Country of Manufacture: USA of USA and Imported Parts

Std Pkg Qty: 100

Unit Qty: 10