



## 4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in. KO & Fifteen TKO's, Raised Ground

By Raco  
Catalog # [257](#)



4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in. KO & Fifteen TKO's, Raised

### Features

- Combination screw heads provide for faster installation
- TKO knockouts allow for design and installation flexibility

### General

Bracket Type	No Bracket
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in.;1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	Box
UPC	050169902578
Wiring System	Conduit

### Dimensions

Actual Depth	2.188 in
Cubic Capacity	42 cu.in
Depth	2.125 in
Height	4.688 in
Raised Ground	Yes
Weight	1.096 lb
Width	4.688 in

### Certifications And Compliance

Certified Listed                      UL Listed

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1500

### Product Assets

[Brochures - Product Solutions for Electrical Prefabrication](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Certifications - UL COC - E195978-5](#)  
[Sales Drawings - 257](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-257-SPEC-EN | REV 5/2024