



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 257DCI2 3" Diecast Emt Insulated Concrete Tight Conn

*Nsi Industries*

Catalog Number	257DCI2
Manufacturer	Nsi Industries
Description	Connector, Compression, Zinc Die Cast, 105 Degree C Insulated Throat, Size 3 Inch
Weight per unit	2.0 (lbs/each)
Product Category	Die Cast Insulated Straight CO

### Features

Connector Type	Compression
insulation	Insulated Throat

### Material, Color, and Finish

Finish	Ball burnish
--------	--------------

### Dimensions and Weight

Size	3
------	---

### Descriptions

Description	3" DIECAST EMT INSULATED CONCRETE TIGHT CONN
extra long description	BPT 257-DCI2 3 IN Comp. Conn. Ins.,
Features	Think Orange: Zinc Advantage –Error-free Performance – meets same stringent UL tests as steel. Bridgeport zinc EMT fittings set the standard for EMT.
Long Description	Connector, Compression, Zinc Die Cast, 105 Degree C Insulated Throat, Size 3 Inch
Product Type	3 In Comp. Conn. Ins., Box Of 12
Special Features	Concrete-Tight

### Manufacturer Information

Brand	Bridgeport
GTIN	00781747162571
Manufacturers Part Number	257-DCI2
UPC	781747162571

### Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	CONNECTOR

### Trade Size

Trade Size	3
------------	---

### Packaging

Carton	12
Weight Per each	2



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Used to join steel EMT to box or enclosure. Concrete-tight. 2 1/2" thru 4" suitable for use with Steel EMT. Insulator rated 105°C. 2-1/2" through 4" also listed for use with Steel and Aluminum Rigid Conduit.

standard

cULus