



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



257I 3" Ins Steel Emt Compression Connector

Bridgeport Fittings

Catalog Number	257I
Manufacturer	Bridgeport Fittings
Description	Emt Compression Connector, 3 In Trade Size, Straight Connection Orientation, Zinc Electro-Plated, Insulated, 4-3/32 In Length, 4-1/32 In Diameter, +105 °C Operating Temperature, 0.251 LB/Ea
Weight per unit	0.2510 (lbs/each)
Product Category	Steel Insulated Straight Compr

Features

Connector Type	Compression
insulation	Insulated Throat
Material	Steel
media	Yes

Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

Dimensions and Weight

Size	3
------	---

Descriptions

Description	3" INS STEEL EMT COMPRESSION CONNECTOR
extra long description	BPT 257-I 3" STEEL INS COMP CONN

Manufacturer Information

Brand	Bridgeport
GTIN	00781747102577
UPC	781747102577

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	3
------------	---

Packaging

Carton	2
Package	10
Weight Per each	0.251

Uses, Certifications, and Standards

Application	Used to join EMT to box or enclosure. Concrete tight.
standard	cULus
Temperature Rating	105?°C