



## 4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in. KO, Six 1-1/4 in., Three TKO's, Raised

By Raco  
Catalog # 259

4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in. KO, Six 1-1/4 in., Three TKO's, Raised



### Features

- Combination screw heads provide for faster installation
- TKO knockouts allow for design and installation flexibility
- Square boxes are used where multiple conductor runs are split into two or more directions to bring power to a number of electrical devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- 42.0 cu. in. capacity
- Made of pre-galvanized steel

### General

Bracket Type	No Bracket
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in.;1-1/4 in.;1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002599
Wiring System	Conduit

### Dimensions

Actual Depth	2.188 in
Cubic Capacity	42 cu.in
Depth	2.125 in
Height	4.688 in
Raised Ground	Yes
Weight	1.106 lb
Width	4.688 in

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1500

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Sales Drawings - RACO-welded-steel-box-infographic](#)  
[Sales Drawings - 259](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-259-SPEC-EN | REV 5/2024