




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



259RTI2 4" Raintight Compression Connector

Nsi Industries

Catalog Number	259RTI2
Manufacturer	Nsi Industries
Description	4" Raintight Insulated Connector, NPT Thread
Weight per unit	2.6 (lbs/each)
Product Category	Die Cast Uninsulated Straight

Features

Connector Type	Compression
insulation	Insulated Throat
media	Yes

Dimensions and Weight

Size	4
------	---

Descriptions

Description	4" RAINLIGHT COMPRESSION CONNECTOR
extra long description	BPT 259-RTI2 4 IN Raintight Ins Con
Long Description	4" Raintight Insulated Connector, NPT THREAD
Product Type	4 In Raintight Ins Connector, Box Of 6
Special Features	The Dual Internal sealing rings create a raintight seal.

Manufacturer Information

Brand	Bridgeport
GTIN	00781747192592
Manufacturers Part Number	259-RTI2
UPC	781747192592

Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	Raintight Compression

Trade Size

Trade Size	4
------------	---

Packaging

Carton	1
Package	6
Weight Per each	2.64



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Compression style connector with internal sealing ring and knockout gasket to create a raintight seal when connecting EMT to box or enclosure. With Bridgeport's newly redesigned Raintight Compression Connectors, 256-RTI2 thru 259-RTI2, contractors can install just one wet location fitting for either thread less Rigid / IMC or EMT. These 4" dual Listed Zinc Alloy fittings come standard with a 105° C temperature rated insulated throat and the words "Rigid / EMT and RAIN TIGHT" clearly cast into the body. Thi

standard

cULus