


# 12983 - 25G25 6PK


### GE crystal clear 25 watt G25 1-pack

Add a decorative touch by using GE Crystal Clear bulbs in chandeliers, sconces or anywhere the bulb is visible.
Add sparkle to your decorative fixtures with GE crystal clear bulbs. The clear glass and elegant filament design provide a decorative touch in fixtures where the bulb is visible. And, GE crystal clear globes' decorative round shape is perfect for illuminating pendant and vanity fixtures

- G25 globe with medium base for use in vanity strips
- Lasts 1.4 years based on 3 hours per day usage
- 190 lumens providing subtle, reassuring<sup>™</sup> light
- 2500K soft white light appearance
- Estimated yearly energy costs \$3.01 based on 3 hours per day \$0.11 per kWh









#### **GENERAL CHARACTERISTICS**

Lamp Type Bulb Base Filament Bulb Finish Rated Life (Vert) Rated Life Bulb Material Primary Application Incandescent - Decorative G25 Medium Screw (E26) CC-6 Clear 1500.0 h 1500.0 hrs Soft glass Globe

#### **PHOTOMETRIC CHARACTERISTICS**

190.0 2500.0 K

### **ELECTRICAL CHARACTERISTICS**

Wattage	25.0
Voltage	120.0

# DIMENSIONS

Initial Lumens

**Color Temperature** 

Maximum Overall Length (MOL) Bulb Diameter (DIA) 4.5000 in(114.3 mm) 3.125 in(79.4 mm)

## **PRODUCT INFORMATION**

Product Code Description Standard Package Standard Package GTIN Standard Package Quantity Sales Unit No Of Items Per Sales Unit No Of Items Per Standard Package UPC 12983 25G25 6PK Case 00043168129831 6 Unit 1 6

043168908825