



GE
Lighting

14866 - GE T10

25T10

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Bulb Finishes and Colors	Clear
Filament	C-8
Rated Life Hours-nominal	1000 h
Primary Application	Standard <General Purpose> Standard <Decorative>
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E26
Bulb Shape	T10

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	10
Initial Lumens-nominal	248 lm

PRODUCT INFORMATION

Product Code	14866
Description	25T10
Alternative Unit Of Measure	CASE

DIMENSIONS

Diameter	1.25 in
----------	---------

ELECTRICAL CHARACTERISTICS

Wattage	25 W
Input Voltage [nom]	130 V