



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2600T 600 Al/Cu 2 Conductor Mechanical Lug

Nsi Industries

Catalog Number	2600T
Manufacturer	Nsi Industries
Description	Mechanical Connector, #2 Awg Conductor Size, 600 MCM Conductor Size, Non-Insulated, Aluminum/Copper Conductor Material, 2 Conductors, +90 °C Operating Temperature, 3.18 In Overall Length, Screw Terminal, 600 V, 0.55 LB/Ea
Weight per unit	0.5500 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Warranty	1 YEAR
----------	--------

Material, Color, and Finish

Color	Aluminum
Finish	Aluminum

Descriptions

Description	600 AL/CU 2 CONDUCTOR MECHANICAL LUG
extra long description	NSI 2-600T EZ-RJ45 Strain Reliefs,
Features	2 Port Aluminum Lug 600 MCM - 2 AWG Aluminum Double Lugs are versatile and reuseable set screw connectors made of 6061T-6 aluminum alloy. Electro tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600 volts, 90 degrees C. UL 486A/B Listed.

Manufacturer Information

Brand	Platinum Tools
GTIN	00662381001245
UPC	662381001245

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Aluminum Double Lug

Packaging

Carton	1
Package	4
Weight Per each	0.55

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	cULus
Temperature Rating	90 C