



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2621I SW Dec 1P 20A 120/277V Grounded I

*Pass & Seymour/Legrand*

Catalog Number	2621I
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Weight per unit	0.1970 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	SP
actuator	Paddle
amperage rating	20
Contact Rating	20Amp, 120/277V
indoor/outdoor	Indoor
insulation	Bare
Load Rating	20 A @ 120/277 VAC
Load Type	Incandescent, CFL, Xenon, Fluorescent, LED, Universal, Halogen
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Paddle
throw type	Single Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	4.2"
------	------

### Descriptions

Description	SW DEC 1P 20A 120/277V GROUNDED I
extra long description	P&S 2621I SW DEC 1P 20A 120/277V GR
Features	Decorator Style
Long Description	Single-Pole, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Product Type	SW Dec 1P 20A 120/277V Grounded I
Special Features	Impact-resistant, cushioned thermoplastic paddle assures smooth quiet, long term operation



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007539332
Manufacturers Part Number	2621-I
UPC	785007539332

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Decorator, Switch

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.197

## Uses, Certifications, and Standards

Application	Commercial/Residential
Mounting standard	WALL UL, CSA, CULUS, UL20