



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2624CW6P L1630C *Ericson MFG*

Catalog Number	2624CW6P
Manufacturer	Ericson MFG
Description	Connector, Polarized; Corrosion Resistant, Water Tight; L16-30R; 480 V 3 Phase; 30 Ampere; 3 Pole; 4 Wire; Grounding; Thermoplastic Polyester Body, Thermoplastic Elastomer Cover; Yellow, Blue; Cord Size 18 to 8 Awg; Approval UI, Csa; Perma-Tite[R] Brand
Weight per unit	0.9000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

Cord Size	18 TO 8 AWG
Current Rating	30 AMPERE
Ground Type	GROUNDING
Material	THERMOPLASTIC POLYESTER BODY, THERMOPLASTIC ELASTOMER COVER
Number of Wires	4 in
Poles	3 in
Voltage Rating	480 V 3 PHASE

Material, Color, and Finish

Color	YELLOW, BLUE
-------	--------------

Descriptions

Commodity Description	PLUGS,CONN,INLETS,OUTLETS,LAMPHOLDR
Description	L1630C
Long Description	CONNECTOR, POLARIZED; CORROSION RESISTANT, WATER TIGHT; L16-30R; 480 V 3 PHASE; 30 AMPERE; 3 POLE; 4 WIRE; GROUNDING; THERMOPLASTIC POLYESTER BODY, THERMOPLASTIC ELASTOMER COVER; YELLOW, BLUE; CORD SIZE 18 TO 8 AWG; APPROVAL UL, CSA; PERMA-TITE[R] BRAND
Product Type	Connector

Manufacturer Information

Brand	Ericson MFG
GTIN	00782862825198
Manufacturers Part Number	2624-CW6P
UPC	782862825198

Taxonomies, Classifications, and Categories

Category Description	SAFETY WIRING DEVICES
Type	POLARIZED



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.9

Uses, Certifications, and Standards

Approval	UL, CSA
Configuration	L16-30R

Ericson NEMA Chart



Face View	NEMA	Electrical Ratings		PERMA-TITE® 2		PERMA-GRIP™	
	Configuration	Amps	Volts	Plugs	Connectors	Plugs	Connectors
2-pole, 3-Wire Grounding							
	5-15	15	125	1510-PW6P	1610-CW6P	1510-PG	1610-CG
	5-20	20	125	1512-PW6P	1612-CW6P	1512-PG	1612-CG
	6-15	15	250	1514-PW6P	1614-CW6P	1514-PG	1614-CG
	6-20	20	250	1516-PW6P	1616-CW6P	1516-PG	1616-CG
	L5-15	15	125	1520-PW6P	1620-CW6P	1520-PG	1620-CG
	L6-15	15	250	1522-PW6P	1622-CW6P	1522-PG	1622-CG
	L7-15	15	277	1524-PW6P	1624-CW6P	1524-PG	1624-CG
	L5-20	20	125	2310-PW6P	2410-CW6P	2310-PG	2410-CG
	L6-20	20	250	2312-PW6P	2412-CW6P	2312-PG	2412-CG
	L7-20	20	277	2314-PW6P	2414-CW6P	2314-PG	2414-CG
3-Pole, 3-Wire Non-Grounding							
	Non-NEMA	20	125/250	2316-PW6P	2416-CW6P	2316-PG	2416-CG
	Non-NEMA	20/10	205/600	2317-PW6P	2417-CW6P	2317-PG	2417-GC
	Non-NEMA	15A/10A	125V/250V	1507-PW6P	1607-CW6P	1507-PG	1607-CG
3-Pole, 4-Wire Grounding							
	L14-20	20	125/250	2320-PW6P	2420-CW6P		
	L15-20	20	250, 3Ø	2322-PW6P	2422-CW6P		
	L16-20	20	480, 3Ø	2324-PW6P	2424-CW6P		
2-Pole, 3-Wire Grounding							
	L5-30	30	125	2510-PW6P	2610-CW6P	2510-PG	2610-CG
	L6-30	30	250	2512-PW6P	2612-CW6P	2512-PG	2612-GC
	L7-30	30	277	2514-PW6P	2614-CW6P	2514-PG	2614-CG
3-Pole, 3-Wire Non-Grounding							
	Non-NEMA	30	125/250	2516-PW6P	2616-CW6P		
3-Pole, 4-Wire Grounding							
	L14-30	30	125/250 3Ø	2520-PW6P	2620-CW6P		
	L15-30	30	250, 3Ø	2522-PW6P	2622-CW6P		
	L16-30	30	480, 3Ø	2524-PW6P	2624-CW6P		
	L17-30	30	600, 3Ø	2526-PW6P	2626-CW6P		
4-Pole, 4-Wire							
	L18-30	30	120/208 3Ø wye	2530-PW6P	2630-CW6P		
4-Pole, 4-Wire Non-Grounding							
	Non-NEMA	30	120/208 3Ø wye	2528-PW6P	2628-CW6P		

WIRING DEVICES