



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2624RED SW Dec 4W 20A 120/277V Grounded RD

Pass & Seymour/Legrand

Catalog Number	2624RED
Manufacturer	Pass & Seymour/Legrand
Description	4-Way, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Weight per unit	0.2540 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	TP 4Way
actuator	Paddle
amperage rating	20
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	Bare
Load Rating	20 A @ 120/277 VAC
Load Type	Universal, Xenon, Halogen, Incandescent, CFL, LED, Fluorescent
Material	Thermoplastic
media	Yes
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	4-Way
Switch Type	Paddle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	4.6x2.5x2.4
------	-------------

Descriptions

Description	SW DEC 4W 20A 120/277V GROUNDED RD
extra long description	P&S 2624RED SW DEC 4W 20A 120/277V
Features	Decorator Style
Long Description	4-way, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Product Type	SW Dec 4W 20A 120/277V Grounded Red
Special Features	Impact resistant back body & frame, cushioned paddle, internal screw plate



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007539646
Manufacturers Part Number	2624-RED
UPC	785007539646

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Switch, Decorator

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.254

Uses, Certifications, and Standards

Application	Residential/Commercial
Mounting standard	WALL CULUS, CSA, UL 20