



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948



2624W SW Dec 4W 20A 120/277V Grounded W *Pass & Seymour/Legrand*

Catalog Number	2624W
Manufacturer	Pass & Seymour/Legrand
Description	4-Way, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Weight per unit	0.2540 (lbs/each)
Product Category	Gen Purpose Switches

Features

amperage rating	20
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	Bare
Load Rating	20 A @ 120/277 VAC
Load Type	Xenon, Fluorescent, Incandescent, LED, Halogen, Universal, CFL
Material	Thermoplastic
media	Yes
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	4-Way
Switch Type	Paddle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	4
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	4.25"
------	-------

Descriptions

Description	SW DEC 4W 20A 120/277V GROUNDED W
extra long description	P&S 2624W SW DEC 4W 20A 120/277V GR
Features	Decorator Style
Long Description	4-way, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Product Type	SW Dec 4W 20A 120/277V Grounded W
Special Features	Impact resistant polycarb back body & frame, cushioned thermoplastic paddle , unique single rocking butterfly contact



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007539653
Manufacturers Part Number	2624-W
UPC	785007539653

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Switch, Decorator

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.254

Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL CULUS, CSA, UL 20