



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



262521 M18 Hackzall Kit W/1 Bat

Milwaukee Electric Tool

Catalog Number	262521
Manufacturer	Milwaukee Electric Tool
Description	
Weight per unit	9.6 (lbs/each)
Product Category	Battery Driven Tools

Features

battery	M12 REDLITHIUM XC
idea granular category code	2380
Stroke Length	3/4 IN
Voltage Rating	51330

Descriptions

Description	M18 HACKZALL KIT W/1 BAT
Product Type	Hackzall Saw Kit, 18 V, M12 Redlithium XC
Special Features	One-handed design provides superior control and versatility over a standard reciprocating saw; Compact size allows for cutting in tight spaces, and light weight makes overhead work easier; QUIK-LOK 1/2 IN universal tang blade clamp offers fast, easy tool free blade changes; Built-In LED light illuminates the work surface while cutting; Compatible with M18 XC high capacity RED LITHIUM batteries and M18 compact RED LITHIUM batteries; Features dual gear anti-vibration system for unmatched comfort and control;

Manufacturer Information

Brand	MILWAUKEE ELECTRIC TOOL
GTIN	00045242200580
Manufacturers Part Number	2625-21
sub brand	HACKZALL
UPC	045242200580

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	Cordless One-Handed Reciprocating Saw Kit

Packaging

Carton	1
Weight Per each	9.55

Uses, Certifications, and Standards

Application	For Used With HACKZALL And SAWZALL Style Blades
-------------	---



Search Milwaukee tool.com

Home > Products > Tools > Cordless Tools > M18™ Cordless LITHIUM-ION System > HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw Kit

SHARE

PRINT

HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw Kit 2625-21

Buy Local

Zip Code



BUY ONLINE

Related Items



Photos

Videos

The Milwaukee Advantage

The HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw (2625-20) features a Patent Pending Dual Gear Anti-Vibration System for unmatched comfort and control as well as light weight design for superior control and versatility. The powerful motor delivers 0-3,000 strokes per minute and a 3/4" stroke length allows for fast cutting through a wide range of material such as wood, metal and PVC. The dual gear anti-vibration system increases control and accuracy. The 2625-21 also features a QUIK-LOK® blade clamp which offers fast and easy blade changes.

Features

One-handed design provides superior control & versatility over a standard reciprocating saw

Compact size allows for cutting in tight spaces, and light weight makes overhead work easier QUIK-LOK® Blade Clamp offers fast, easy tool free blade changes for SAWZALL® Blades & HACKZALL® Blades

Built-In LED light illuminates the work surface while cutting
Compatible with M18™ XC High Capacity REDLITHIUM™ Batteries and M18™ Compact REDLITHIUM™ Batteries

Specifications

Voltage	18V
Speed	0-3000 SPM
Stroke Length	¾"
Blade Clamp	QUIK-LOK™ Universal
Trigger	Variable
Battery	LITHIUM-ION
Tool Length	13 in
Tool Weight	4.1 lbs
Shipping Weight	9.87 lbs

Includes

- 2625-20 HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw
- (1) M18™ XC High Capacity REDLITHIUM™ Battery
- 1-Hour Charger
- SAWZALL® Blade
- Contractor Bag



6" 18 TPI Sawzall® Blades (50 Pk)



M12 Hackzall™ Blade-10 PC. Set



M18™ XC High Capacity REDLITHIUM™ Battery

[+ More Related Items](#)

Related Articles

[Milwaukee® Introduces New Hackzall® M18™ Cordless One-Handed Recip Saw](#)

Sign Up for the Heavy Duty Club



Products

New Products & Offers
Tools
Accessories

Parts & Service

e-SERVICE Tool Repair
Test & Measure Service
Find a Service Center

News & Media

Press Releases
Milwaukee Ink
MilwaukeeCain.com

About Us

Milwaukee Story
Careers
Locations

Email

First Name

Zip/Postal Code

SUBMIT >

Test & Measurement
Milwaukee Gear
Print Current Catalog

Download Manuals
Parts Pricing
Milwaukee Warranty
Lightning Max Repair
FAQ's

Product Reviews
Media Center
Media Inquiries

Buy Now
Contact Us