Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory

263521

Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Ivory





features & benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14
 #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

specifications

General Info

Color: Ivory

Type: Receptacles Duty: Heavy Duty

Special Features: Back, Side Wire

Style: Decorator

Listing Agencies/Third Party Information

CSA Standard: Yes cUL Standard: Yes Federal Spec: Yes

Fed Spec Number: WC596 UL Listing No: UL498 UL Standard: Yes UN SPS C: 39121406

Dimensions

Depth U S: 0.833" Height U S: 3.281" Width U S: 1.322"

Technical Information

Amps: 20 Amp Volts: 125V Volts A C: 125 Capacity: Duplex

Grade Type: Specification

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant