ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



267RT 3" Diecast Emt Raintight Compression Coupling

Nsi Industries

Catalog Number	267RT
Manufacturer	Nsi Industries
Description	3" Raintight Coupling
Weight per unit	2.2 (lbs/each)
Product Category	Liquid Tight Fittings

Features

Connector Type	Compression
media	Yes
outside diameter	4.08

Dimensions and Weight

Length	4

Descriptions

Description	3" DIECAST EMT RAINTIGHT COMPRESSION COUPLING
extra long description	BPT 267-RT 3 IN Raintight Cplg, Box
Features	Think Orange: Quality In, Water Out. Listed for Damp or Wet Locations.
Long Description	3" Raintight Coupling
Product Type	3 In Raintight CPLG, Box Of 12
Special Features	With Bridgeport's newly redesigned Raintight Compression Couplings, 266-RT through 269-RT, contractors can install just one wet location fitting for either thread less Rigid / IMC or EMT.

Manufacturer Information

Brand	Bridgeport
GTIN	00781747142672
Manufacturers Part Number	267RT
UPC	781747142672

Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	Raintight

Trade Size

Trade Size	3

Packaging

Carton	12
Weight Per each	2.208

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	These 3” dual Listed Zinc Alloy fittings come standard with a 105° C temperature rated insulated throat and the words “Rigid / EMT and RAINTIGHT” clearly cast into the body. This marking helps the AHJ to precisely confirm the products intended use. Patented
standard	cULus