

Eaton 276LA

Catalog Number: 276LA

Eaton commercial grade combination switch, Stand, #14 - #12 AWG, 15A, Commer, 120/277V, bk and sd wiring, togg, Maint closure, Screw, Brass, It almd, -20-60°C, (2) 3-way, dplx, thermoplas



General specifications

Product Name	Catalog Number
Eaton commercial grade combination switch	276LA
	UPC
	032664583322
Product Length/Depth	Product Height
4.25 in	1.88 in
Product Width	Product Weight
1.75 in	0.2 lb
Compliances	Certifications
RoHS Compliant	cULus Listed NOM

Product specifications

Connector type

Screw

Switch type

(2) Three-way

Configuration

(2) toggle

Closure type

Maintained

Color

Light almond

Wiring method

Back and side

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Contact type

Brass

Type

Standard

Device grade

Commercial

Style type

Duplex

Operating temperature

-20 to 60 °C

Number of ways

(2) Three-way

Voltage rating

120/277 V

Resources

Catalogs

[Arrow Hart Buyers Guide Section E](#)

Specifications and datasheets

[Eaton Specification Sheet - 276LA](#)

Application
Commercial

Actuator
Toggle



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)