

# Eaton 277V-BOX

Catalog Number: 277V-BOX

Eaton commercial grade combination switch, Neon pil lgt, Stand, #14 - #12 AWG, 15A, Commer, 120V (Switch), 125V (pil lgt), bk and sd wiring, togg, Maint closure, Screw, Brass, Ivy, -20-60°C, 1-pole, dplx, thermoplas, 1 / 25W



## General specifications

Product Name	Catalog Number
Eaton commercial grade combination switch	277V-BOX
	UPC
	032664750328
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
1.08 in	0.2 lb
Compliances	Certifications
RoHS Compliant	cULus Listed

## Product specifications

### Connector type

Screw

### Switch type

Single-pole

### Configuration

Toggle switch

125V pilot light

### Closure type

Maintained

### Color

Ivory

### Wiring method

Back and side

### Wattage

1/25 W

### Material

Thermoplastic

### Mounting method

Flush

### Allowable wire size

#14-12 AWG

### Amperage Rating

15A

### Number Of Poles

Single-pole

### Contact type

Brass

### Type

Standard

### Device grade

Commercial

### Style type

Duplex

### Illumination

Neon pilot

## Resources

### Catalogs

[Arrow Hart Buyers Guide E-18](#)

### Specifications and datasheets

[Eaton Specification Sheet - 277V-BOX](#)

#### Operating temperature

-20 to 60 °C

#### Voltage rating

120V (Switch)

125V (Pilot Light)

#### Application

Commercial

#### Torque rating

14 lbf-inch

#### Actuator

Toggle



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)