



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

475 Boardwalk
78119-2604, TX Kenedy
Phone: 830-299-4593
Fax: 830-583-9886



27W48 Turnlok Conn IP67 20A 250V L620R

Pass & Seymour/Legrand

Catalog Number	27W48
Manufacturer	Pass & Seymour/Legrand
Description	Locking Watertight Connector, 20 Amp 250 Volt, Nema Configuration L6-20, Multipoint Sealing System Provides Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated.
Weight per unit	0.8300 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	20
Cord Type	12/3 SJ, 14/3 S to 10/3 S, .475" min to .720" max
indoor/outdoor	Both
ip rating	IP67
Material	Rubber
Number of Phases	1.0
Number of Wires	3.0
Phase	Single
Poles	2
Voltage	250.0 V
Voltage Rating	125
Wire Size	14 - 10 AWG

Material, Color, and Finish

Color	Yellow
-------	--------

Descriptions

Description	TURNLOK CONN IP67 20A 250V L620R
extra long description	P&S 27W48 TURNLOK CONN IP67 20A 250
Features	Watertight
Long Description	Locking Watertight Connector, 20 amp 250 volt, NEMA Configuration L6-20, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.
Product Type	Turnlok Conn IP67 20A 250V L620R
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

475 Boardwalk
78119-2604, TX Kenedy
Phone: 830-299-4593
Fax: 830-583-9886

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033779
Manufacturers Part Number	27W48
UPC	785007033779

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	CONNECTOR

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.83

Uses, Certifications, and Standards

Application	High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings Ideal for washdown areas — rated wa
environmental conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized
nema rating	NEMA 4X, NEMA 6P
Operating Temperature	-40°-60°C
standard	UL Listed, CSA Listed