

MEDIUM BASE LAMPHOLDER



280WH | Pass & Seymour

FEATURES & BENEFITS

Medium base, phenolic, pullchain, 4 terminals with tri-drive screws, fits 3 1/4 and 4" boxes, with cage necks. White.



- Quality Materials.
- Durability.
- Time-tested design.

SPECIFICATIONS

GENERAL INFO

Type: Incandenscent Medium Base Lampholder

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: Yes CUL Listing No: No

cULus: Yes cURus: No Federal Spec: No UL Listing No: Yes UN SPSC: 39111803

UR: No

DIMENSIONS

Diameter (US): 4.5" Height (Metric): 2.00"

TECHNICAL INFORMATION

Volts: 250V Volts (AC): 250 Watts: 250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA Buy American Act Status: Trade Agreement Act Compliant