

Eaton 2867-BOX

Catalog Number: 2867-BOX

Eaton straight blade plug , #18-12 AWG, 15A, Commercial, 125V, Back wire, Yellow, Brass, Armored vinyl, 5-15P, Two-pole, three-wire, grounding, Screw, 0.25-0.63", Vinyl, ED Box

General specifications



Product Name

Eaton straight blade plug

Catalog Number

2867-BOX

UPC

032664325809

Product Length/Depth

1.519 in

Product Height

2.524 in

Product Width

1.519 in

Product Weight

0.115 lb

Warranty

Refer to warranty document.

Compliances

RoHS Compliant

Certifications

cULus Listed

NOM

Product specifications

Special features

Armored

Device type

Plug

Color

Yellow

Face/body material

Armored vinyl

Wiring method

Back wire

Features

Armored

Material

Vinyl

Allowable wire size

#18-12 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Armored plug

Device grade

Commercial specification grade

NEMA configuration

5-15P

Style type

Straight body

Design type

Straight blade

Connection type

Screw

Number of wires

Resources

Catalogs

Residential Buyers Guide B-49

Multimedia

Commercial and residential straight blade vinyl receptacles

Specifications and datasheets

Eaton Specification Sheet - 2867-BOX

Receptacle type

Two-pole, three-wire, grounding

Cord range

0.25-0.63"

Voltage rating

125V

Application

Commercial

Torque rating

15 lbf-inch

Packaging type

ED Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia