

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301420036

Status:

Active

Overview:

Heavy-Duty Industrial Wiring Devices

Description:

Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L14-30, 125V/250V



Documents:	
RoHS Certificate of Compliance (PDF)	Product Literature (PDF)
Agency Certification	
CSA	LR6837
UL	E10176
General	
Product Family	Wiring Devices
Series	130142
IP Rating	N/A
NEMA Configuration	NEMA L14-30
Overview	Heavy-Duty Industrial Wiring Devices
Product Literature Order No	987650-8068
Product Name	Super-Safeway
Receptacle Type	N/A
Specialty	N/A
Type	Plug
UPC	78678870435
Woodhead	Yes
Physical	
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Locking Blade	Yes
Poles	3-pole/4-wire
Electrical	
Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V / 250V
Material Info	
Engineering Number	2874

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130142 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301420036](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L14-30, 125V/250V

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
UL E10176

General

Product Family Wiring Devices
Series [130142](#)
IP Rating N/A
NEMA Configuration NEMA L14-30
Overview [Heavy-Duty Industrial Wiring Devices](#)
Product Literature Order No 987650-8068
Product Name Super-Safeway
Receptacle Type N/A
Specialty N/A
Type Plug
UPC 78678870435
Woodhead Yes

Physical

Flange No
Flip Lid No
Gender Male
Length N/A
Locking Blade Yes
Poles 3-pole/4-wire

Electrical

Cord Type N/A
Current - Maximum per Contact 30.0A
GFCI No
Lighted Connector No
Voltage - Maximum 125V / 250V

Material Info

Engineering Number 2874



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130142](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION