

Eaton 2887-BOX

Catalog Number: 2887-BOX

Eaton straight blade connector , #18-12 AWG, 15A, Commercial, 125V, Back wire, Yellow, Brass, Armored vinyl, 5-15R, Two-pole, three-wire, grounding, Screw, 0.25-0.63", Vinyl, ED Box



General specifications

Product Name	Catalog Number
Eaton straight blade connector	2887-BOX
UPC	Product Length/Depth
032664326103	2.6 in
Product Height	Product Width
1.5 in	1.5 in
Product Weight	Compliances
0.16 lb	RoHS Compliant
Certifications	
cULus Listed	
NOM	

Product specifications

Special features

Armored

Device type

Connector

Color

Yellow

Face/body material

Armored vinyl

Wiring method

Back wire

Features

Armored

Material

Vinyl

Allowable wire size

#18-12 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Armored connector

Device grade

Commercial specification grade

NEMA configuration

5-15R

Style type

Straight body

Design type

Straight blade

Connection type

Screw

Number of wires

Resources

Catalogs

Residential Buyers Guide B-49

Multimedia

Commercial and residential straight blade vinyl receptacles

Specifications and datasheets

Eaton Specification Sheet - 2887-BOX

Receptacle type

Two-pole, three-wire, grounding

Cord range

0.25-0.63"

Voltage rating

125V

Application

Commercial

Torque rating

15 lbf-inch

Packaging type

ED Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia