



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



28W09 Turnlok Plug IP67 4W 30A 120/208V Non

Pass & Seymour/LeGrand

Catalog Number	28W09
Manufacturer	Pass & Seymour/LeGrand
Description	Locking Watertight Non-Grounding Plug, 30AMP 3Y 120/208VOLT, Multipoint Sealing System Provides Environmental Protection Of: Nema 4, 4X, 6, 6P and IP67 Rated.
Weight per unit	0.5250 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
Cord Type	12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max
indoor/outdoor	Both
ip rating	IP67
Material	Rubber
Number of Phases	1.0
Number of Wires	4
Phase	1
Poles	4-Way
Voltage	120/208 V
Voltage Rating	120/208
Wire Size	12-6

Descriptions

Description	TURNLOK PLUG IP67 4W 30A 120/208V NON
extra long description	P&S 28W09 TL PLUG IP67 4W 30A 120/
Features	Watertight
Long Description	Locking Watertight Non-Grounding Plug, 30amp 3Y 120/208volt, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P and IP67 rated.
Product Type	TL Plug IP67 4W 30A 120/208V Non
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033137
Manufacturers Part Number	28W09
UPC	785007033137



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Locking, Plug

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.525

Uses, Certifications, and Standards

Application	High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings Ideal for washdown areas — rated wa
environmental conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized
nema rating	Non-NEMA
Operating Temperature	-40°-60°C
standard	UL Listed, CSA Listed