



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1725 East Highway 82
76240-0000, TX Gainesville
Phone: 940-612-1388
Fax: 940-612-1499



28W76 Turnlok Plug IP67 30A 3PH 480V L1630P

Pass & Seymour/Legrand

Catalog Number	28W76
Manufacturer	Pass & Seymour/Legrand
Description	Locking Watertight Plug, 30AMP 3 480 Volt, Nema Configuration L16-30, Multipoint Sealing System Provides Environmental Protection Of: Nema 4, 4X, 6, 6P and IP67 Rated.
Weight per unit	0.8300 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
Cord Type	12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max
indoor/outdoor	Both
ip rating	IP67
Material	Rubber
Number of Phases	3.0
Number of Wires	4
Phase	3
Poles	3-way
Voltage	480.0 V
Voltage Rating	480
Wire Size	12-6

Descriptions

Description	TURNLOK PLUG IP67 30A 3PH 480V L1630P
extra long description	P&S 28W76 TL PLUG IP67 30A 3PH 480V
Features	Watertight
Long Description	Locking Watertight Plug, 30amp 3 480 volt, NEMA Configuration L16-30, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P and IP67 rated.
Product Type	TL Plug IP67 30A 3PH 480V L1630P
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033519
Manufacturers Part Number	28W76
UPC	785007033519



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1725 East Highway 82
76240-0000, TX Gainesville
Phone: 940-612-1388
Fax: 940-612-1499

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Locking, Plug

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.83

Uses, Certifications, and Standards

Application	High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings Ideal for washdown areas — rated wa
environmental conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized
nema rating	L16-30P
Operating Temperature	-40°-60°C
standard	UL Listed, CSA Listed