



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 28W77 TL Plug IP67 4W 30A 600V L1730P

*Pass & Seymour/Legrand*

Catalog Number	28W77
Manufacturer	Pass & Seymour/Legrand
Description	30A 600V L1730P IP67 Turnlok Plug
Weight per unit	0.8300 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	30
Cord Type	12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max
Material	Rubber
Number of Wires	4
Phase	1
Poles	3
Voltage Rating	600
Wire Size	12 - 6

### Descriptions

Description	TL PLUG IP67 4W 30A 600V L1730P
extra long description	P&S 28W77 TL PLUG IP67 4W 30A 600V
Long Description	30A 600V L1730P IP67 Turnlok Plug
Product Type	TL Plug IP67 4W 30A 600V L1730P
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033403
Manufacturers Part Number	28W77
UPC	785007033403

### Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	LOCKING PLUG

### Packaging

Carton	1
Package	10
Weight Per each	0.83



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

### Application

High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors | Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings | Ideal for washdown areas — rated wa

### environmental conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized

### nema rating

L17-30P

### standard

UL Listed, CSA Listed