



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



29W74 Turnlok Conn IP67 30A 125/250V L1430R

Pass & Seymour/Legrand

Catalog Number	29W74
Manufacturer	Pass & Seymour/Legrand
Description	Locking Watertight Connector, 30AMP 125/250VOLT, Nema Configuration L14-30, Multipoint Sealing System Provides Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated.
Weight per unit	0.8150 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
Cord Type	12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max
indoor/outdoor	Both
ip rating	IP67
Material	Rubber
Number of Phases	1.0
Number of Wires	4.0
Phase	Single
Poles	3-way
Voltage	277/480 VAC
Voltage Rating	125/250
Wire Size	12 - 6 AWG

Material, Color, and Finish

Color	Yellow
-------	--------

Descriptions

Description	TURNLOK CONN IP67 30A 125/250V L1430R
extra long description	P&S 29W74 TL CONN IP67 30A 125/250V
Features	Watertight
Long Description	Locking Watertight Connector, 30amp 125/250volt, NEMA Configuration L14-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.
Product Type	TL Conn IP67 30A 125/250V L1430R
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033762
Manufacturers Part Number	29W74
UPC	785007033762

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	CONNECTOR

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.815

Uses, Certifications, and Standards

Application	High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings Ideal for washdown areas — rated wa
environmental conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized
nema rating	NEMA 4X, NEMA 6P
Operating Temperature	-40°-60°C
standard	UL Listed, CSA Listed