



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



29W75 Turnlok Conn IP67 30A 3PH 250V L1530R

Pass & Seymour/Legrand

Catalog Number	29W75
Manufacturer	Pass & Seymour/Legrand
Description	Locking Watertight Connector, 30AMP 3 250VOLT, Nema Configuration L15-30, Multipoint Sealing System Provides Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated.
Weight per unit	0.8300 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
Cord Type	12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max
indoor/outdoor	Both
ip rating	IP67
Material	Rubber
Number of Phases	3.0
Number of Wires	4.0
Phase	Three
Poles	3-way
Voltage	125.0 V
Voltage Rating	250
Wire Size	12 - 6 AWG

Material, Color, and Finish

Color	Yellow
-------	--------

Descriptions

Description	TURNLOK CONN IP67 30A 3PH 250V L1530R
extra long description	P&S 29W75 TLCONN IP67 30A 3PH 250V
Features	Watertight
Long Description	Locking Watertight Connector, 30amp 3 250volt, NEMA Configuration L15-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.
Product Type	Tlconn IP67 30A 3PH 250V L1530R
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033496
Manufacturers Part Number	29W75
UPC	785007033496

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	CONNECTOR

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.83

Uses, Certifications, and Standards

Application	High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings Ideal for washdown areas — rated wa
environmental conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized
nema rating	L15-30R
Operating Temperature	-40°-60°C
standard	UL Listed, CSA Listed