



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2BLT240LADSMGZ 2BLT2 40L Adsm GZ10 LP840

Lithonia Lighting - Acuity

Catalog Number	2BLT240LADSMGZ
Manufacturer	Lithonia Lighting - Acuity
Description	Lith 2BLT2 40L Adsm GZ10 LP840 Bask
Weight per unit	11.1 (lbs/each)
Product Category	Lighting

Features

average life	60,000
dimmmable	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	4000 LM
Material	Steel
Maximum Operating Temperature	25
Power Source	Hardwired
Shape	Square
Voltage Rating	120-277
Warranty	5
Wattage	31.7

Material, Color, and Finish

Color	White
color rendering index (cri)	80
color temperature	4000
Finish	Matte
Lens Color	WHITE
Lens Material	Acrylic
Style	Traditional

Dimensions and Weight

Height	1.6
Length	23.75
Width	23.75

Descriptions

Construction	New Construction,Remodel
Description	2BLT2 40L ADSM GZ10 LP840
Features	Design Select
Long Description	LITH 2BLT2 40L ADSM GZ10 LP840 Bask
Product Type	Troffer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00193047046411
Manufacturers Part Number	2BLT2 40L ADSM GZ10 LP840
UPC	193047046411

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
----------------------	--

Trade Size

aperture size	2x2
---------------	-----

Packaging

Carton	1
Weight	9.312
Weight Per each	11.1

Uses, Certifications, and Standards

Application	Clean Room, Education, Government, Healthcare, Hospitality, House of Worship, Offices & Banks, Patient Room, Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSA