



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

110 Success Blvd
79029-0000, TX Dumas
Phone: 806-934-4805
Fax: 806-717-2052



3004040L Holesaw T4 40L 2 1/2 64MM 1/BX

Black & Decker Inc.

Catalog Number	3004040L
Manufacturer	Black & Decker Inc.
Description	Hole Saw, Constant Pitch Type; Wood, Metal, Mild Steel, Stainless Steel, Cast Iron, Brass, Aluminum Cut Material; Bi-Metal Blade Material; 2-1/2 Inch Diameter
Weight per unit	0.4510 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Speed Rating	135 RPM (Mild Steel), 65 RPM (Stainless Steel), 90 RPM (Cast Iron), 180 RPM (Brass), 205 RPM (Aluminum)
Supplied with Arbor	No
Supplied with Pilot Drill	NO

Material, Color, and Finish

Blade Material	Bi-Metal
Cut Material	Wood, Metal, Mild Steel, Stainless Steel, Cast Iron, Brass, Aluminum

Dimensions and Weight

Diameter	2-1/2 INCH
----------	------------

Descriptions

Additional Information	Pipe Entrance Size 2 Inch; Use 2L/6L (Snap Back), 2L/3L/6L/7L (Standard) Arbor; Applicable Standard OSHA, 29 CFR 1910.1200
Commodity Description	POWER TOOLS BITS, PARTS, ACCESSORIES
Description	HOLESAW T4 40L 2 1/2 64MM 1/BX
extra long description	WOOD, METAL CUT MATERIAL; BI-METAL BLADE MATERIAL; 2-1/2 INCH DIAMETER; LARGER, SHARPER TEETH TYPE; SPEED SLOT[R] BRAND; PIPE ENTRANCE SIZE 2 INCH; USED ON 2L, 6L (SNAP-BACK), 2L, 3L, 6L OR 7L (STANDARD) ARBOR
Long Description	HOLE SAW, CONSTANT PITCH TYPE; WOOD, METAL, MILD STEEL, STAINLESS STEEL, CAST IRON, BRASS, ALUMINUM CUT MATERIAL; BI-METAL BLADE MATERIAL; 2-1/2 INCH DIAMETER
Product Type	Hole Saw

Manufacturer Information

Brand	SPEED SLOT[R], T3[TM]
GTIN	00082472300406
Manufacturers Part Number	3004040L
UPC	082472300406



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

110 Success Blvd
79029-0000, TX Dumas
Phone: 806-934-4805
Fax: 806-717-2052

Taxonomies, Classifications, and Categories

Category Description BITS, BLADES, AND HOLE SAWS

Type CONSTANT PITCH

Packaging

Carton 1

Weight Per each 0.451