

ELLIOTT ELECTRIC SUPPLY 2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



30059 I-Temp Wire-Nut Wire Conn, 59B Black, 100/Box *Ideal*

Catalog Number	30059
Manufacturer	Ideal
Description	Ideal, Wire Connector, Wire-Nut, High Temperature Twist-On, Number Of Conductors: 1 to 6, Conductor Range: 22 - 12 Awg, Min 2 - 20, Max 3-14, Color: Black, Material: Thermoplastic Polyester, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-0 Flame-Retardant Shell Rated At 150 Deg C (302 F), Model Number: 59B, Width: 31/64 In, Height: 1-1/16 In
Weight per unit	0.0070 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts
Features	
Material	THERMOPLASTIC POLYESTER
media	Yes
Voltage Rating	600
Material, Color, and Finish	
Color	Black



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

_	•		
11000	rin	TIAR	•
Desc			17
-			

minimum qty

Weight Per each

Packaging

Carton

Descriptions	
Description	I-TEMP WIRE-NUT WIRE CONN, 59B BLACK, 100/BOX
extra long description	IDEAL 30-059 WIRENUT 59B BLK 100PC
Features	The IDEAL Wire-Nut Wire Connector set new standards for innovation, quality and convenience when it was first introduced in 1928. As the first screw-on wire connector in America, it literally set the industry standard for years to come. With a fixed, square-wire spring and a positive grip shell, the Wire-Nut is perfect to twist-on with fingers for a secure connection that will last. The refined wire range makes it the best choice for fine stranded wire applications. The Wire-Nut also features a tough, flame
Long Description Product Type	IDEAL, Wire Connector, Wire-Nut, High Temperature Twist-On, Number Of Conductors: 1 to 6, Conductor Range: 22 - 12 AWG, Min 2 - 20, MAX 3-14, Color: Black, Material: THERMOPLASTIC POLYESTER, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-0 Flame-Retardant Shell Rated At 150 DEG C (302 F), Model Number: 59B, Width: 31/64 IN, Height: 1-1/16 IN Wirenut 59B BLK 100PC BX
Special Features	Deep Skirt Helps Protect Against Flash-Over; Features: Fixed, Square-Wire Spring Creates Its Own Threads Maintains A Secure Positive Grip That Will Not Relax Over Time; Height: 1-1/16 IN; Model Number: 59B; No Pre-Twisting Required Positive Grip Design Provides Fast, Easy Installation; Reusable For Easy Circuit Changes And Additions; Tough, UL94V-0 Flame-Retardant Shell Rated At 150 Degree C (302 Degree F); UL Listed To 486C And CSA Certified To C22.2 #188; Width: 31/64 IN
Nanufacturer Information	
Brand	Ideal
GTIN	00783250300594
Manufacturers Part Number	30-059
UPC	783250300594
axonomies, Classifications, and	Categories
	WIRE NUTS
Туре	High Temperature Twist-On
vailability	
	100

100

100

0.007



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

os, con inications, and otalidar	u o
Application	Insulating or Joining 2 or more conductors in conditions where extreme heat buildup occurs such as high wattage fixtures and signs.
environmental conditions	Tough, UL 94V-0 Flame-Retardant Shell Rated At 150 DEG C (302 F)
standard	CSA Certified to C22.2 #188, UL Listed to 486C