



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



300GC120 Selectone Speaker/Amplifier, 120VAC, Gain Control

Federal Signal Corp.

Catalog Number	300GC120
Manufacturer	Federal Signal Corp.
Description	Selectone 15 Watt Amplified Speaker, 120VAC, Gray - Available In 24VAC/DC, 120VAC and 240VAC. Built-In Gain Control, Adjustable Between 0 DbA to 110 DbA At 10 Feet (0 DbA to 120 DbA At 1 Meter). Cast Copper Free Aluminum Housing, Spun Aluminum Projector. Indoor or Outdoor Use. Type 3R, IP54 Enclosure. Digital Signal Amplification. Fused Input and Output. CSFM Approved. UL and CUL Listed.
Weight per unit	6.7 (lbs/each)
Product Category	Sound & Audio Systems

Features

dimensions	12.4 H x 7.9 W x 8.5 D
Material	Die-Cast Aluminum
Operating Current	0.20
Operating Voltage	120VAC 50-60Hz
Output Level	15

Material, Color, and Finish

Color	Gray
-------	------

Descriptions

Description	SELECTONE SPEAKER/AMPLIFIER, 120VAC, GAIN CONTROL
extra long description	FED-SIG 300GC-120 SELECTONE 15W AMP
Long Description	SelecTone 15 Watt Amplified Speaker, 120VAC, Gray - Available in 24VAC/DC, 120VAC and 240VAC. Built-in gain control, adjustable between 0 dBa to 110 dBa at 10 feet (0 dBa to 120 dBa at 1 meter). Cast copper free aluminum housing, spun aluminum projector. Indoor or outdoor use. Type 3R, IP54 enclosure. Digital signal amplification. Fused input and output. CSFM Approved. UL and cUL Listed.
Product Type	Selectone 15W Amplified Speaker 120V
Special Features	Digital Signal Amplification

Manufacturer Information

Brand	Federal Signal
GTIN	00782979200215
Manufacturers Part Number	300GC-120
UPC	782979200215



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	SECURITY & FIRE ALARM SYSTEMS
Type	Amplified Speaker

Packaging

Carton	1
Weight Per each	6.7

Uses, Certifications, and Standards

Application	Indoor/Outdoor
Enclosure	Type 3R, IP54
Mounting	SURFACE
Operating Temperature	-67 to 150
standard	UL Listed/cUL Listed/CSFM Approved