



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948



300MIF 300W 130V Incan PS30 FRST Med Base

Sylvania-Ledvance

Catalog Number	300MIF
Manufacturer	Sylvania-Ledvance
Description	Incandescent PS30 Bulb Shape Inside Frost Finish Medium Aluminum Base 300WATT 130VOLT 60BULBS Per Case 1BULBS Per Package
Weight per unit	0.2700 (lbs/each)
Product Category	Line A, P, PS Shape Lamps

Features

average life	750
Base	Medium
Lamp Type	Incandescent
lumens	5,760
Shape	PS30
Voltage	130.00 V
Voltage Rating	130
Wattage	300

Material, Color, and Finish

color rendering index (cri)	100
color temperature	2850
Finish	Inside Frost

Descriptions

Description	300W 130V INCAN PS30 FRST MED BASE
extra long description	SYL 300M/IF-130V/15739 300MIF 130V
Long Description	Incandescent PS30 Bulb Shape Inside Frost Finish Medium Aluminum Base 300Watt 130Volt 60Bulbs Per Case 1Bulbs Per Package
Product Type	300MIF 130V 60/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135157394
Manufacturers Part Number	300M/IF-130V/15739
UPC	046135157394

Taxonomies, Classifications, and Categories

Category Description	INCANDESCENT
Type	INCANDESCENT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948

Packaging

Carton	1
Package	60
Weight Per each	0.27