



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

300T3QCL130V 300W 130V T3 Double End Quartz Halogen Lamp

Sylvania-Ledvance

Catalog Number	300T3QCL130V
Manufacturer	Sylvania-Ledvance
Description	
Weight per unit	0.0300 (lbs/each)
Product Category	Reflector Double Ended T Shape

Features

average life	2000 SQ-FT
Base	R7s
dimnable	Yes Yes/No
lumens	6k lm
Shape	T3
start type	Instant
Voltage Rating	130 WTT
Wattage	300 VAC

Material, Color, and Finish

color rendering index (cri)	100 Wrms
Finish	Clear

Descriptions

Description	300W 130V T3 DOUBLE END QUARTZ HALOGEN LAMP
Product Type	300T3QCL 130V 20/CS 1/Sku

Manufacturer Information

Brand	Sylvania (Usc)
GTIN	00046135590009
Manufacturers Part Number	300T3Q/CL-130V/59000
sub brand	Double End
UPC	046135590009

Taxonomies, Classifications, and Categories

Category Description	QUARTZ
Type	HALOGEN

Packaging

Carton	1
Package	20
Weight Per each	0.03

Uses, Certifications, and Standards

Application	Medium Screwbase or bi-pin
-------------	----------------------------



Product Number: 59000

Order Abbreviation: 300T3Q/CL 130V

General Description: Tungsten Halogen Double End T3 Quartz Clear Finish RSC 300Watt 130Volt

Product Information

Abbrev. With Packaging Info.	300T3QCL 130V 20/CS 1/SKU
Approx. Lumens	6000
Average Rated Life (hr)	2000
Base	R7s
Bulb	T3
Class	C (gas)
Color Rendering Index (CRI)	100
Diameter (in)	0.394
Diameter (mm)	10.00
Ecologic	YES
Family Brand Name	Double End
Filament	CC-8
Lamp Finish	Clear
Maximum Overall Length - MOL (in)	4.688
Maximum Overall Length - MOL (mm)	119
Nominal Voltage (V)	130.00
Nominal Wattage (W)	300.00

Footnotes

- For use where seal temperature does not exceed 650F.
- A suitable protective shield, screening technique, or both must be used to protect people and surroundings from the possibility of a lamp shattering and from possible ultraviolet radiation.