



Catalog Number
Notes
Type

Contractor Select™

# L3/L3R

## 4" Incandescent Line-Voltage Housing and Trims



### L3

Approved for direct burial in insulation and all ceiling and wiring types, these air-tight 4" recessed incandescent housings are rated IC/Non-IC for 2x8 and 2x6 new construction (L3) or remodel (L3R) applications. New construction housings include factory-installed captive bar hangers that span up to 24 o.c. and feature a stepped shank nail with integral T-bar locks. The socket clips to trim to ensure proper and consistent lamp position.

#### FEATURES:

- Damp location listed
- Vertical adjustment of housing allows for flush mounting with ceiling face.
- Suitable for ceilings up to 1-1/2" thick
- Trim options include 4" Open, Baffle, Eyeball and PAR30 WETlite.
- All trims are available in a white finish.



3H2O



3O1



3B1W



3E1



### Housings

Catalog Number	UPC	Description	Lamp Source	Voltage	Socket	Pallet Qty
L3 R6	745973345313	4" Airtight IC/Non-IC New Construction Housing	Incandescent	120V	E26 Screw Shell	144
L3R R6	745973345566	4" Airtight IC/Non-IC Remodel Housing	Incandescent	120V	E26 Screw Shell	312

### Trims

Catalog Number	UPC	Description	Flange Range	Finish	Lamp Included	Pallet Qty
3O1 R12	745975234158	4" Open Trim	Wide	White	No	1344
3B1W R24	745975234264	4" Baffle Trim	Wide	White	No	1536
3E1 R6	745973752937	4" Eyeball Trim	Narrow	White	No	756
3H2O R6	745975281060	4" PAR30 WETlite Trim	Stepped	White	No	630

<b>Accessories L3R6:</b> Order as separate catalog number.	
ATK3 R6	Airtight trim kit



## Specifications

### L3

#### INTENDED USE:

Recessed housing rated IC or Non-IC. For new construction only. Approved for all ceiling and wiring types. Approved for direct burial in insulation

#### INSTALLATION

Air-tight housing suitable for air-tight installations. Refer to energy codes for proper installations. 2x8 and 2x6 wood joist or T-bar installation. Expandable bar hangers allow for off-center mounting in wood joist or T-bar ceilings. Length of 25-1/2" maximum 13-1/4" minimum or cut to fit 5-1/2" on center joist construction. Vertical adjustment of housing allows for flush mounting with ceiling face. Suitable for ceilings up to 1-1/2" thick.

#### LISTINGS:

UL Listed to US and Canadian safety standards. Damp location listing (See trim selection for wet location listing).

#### WARRANTY:

1-year limited warranty. Complete warranty terms located at:  
[www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

**Note:** Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

### L3R

#### INTENDED USE:

Recessed housing rated IC or Non-IC. For remodel construction only.

#### INSTALLATION

Socket to trim interface. Retaining clips pull and snap onto top of reflector to hold trim inside housing. Approved for factory assembled wiring only. Approved for direct burial in insulation. Air-tight housing suitable for air-tight installations. Refer to energy codes for proper installations...

#### LISTINGS:

UL Listed to US and Canadian safety standards. Damp location listing (See trim selection for wet location listing)..

#### WARRANTY:

1-year limited warranty. Complete warranty terms located at:  
[www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

**Note:** Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

## Dimensions

All dimensions are inches (centimeters) unless otherwise indicated.

Height: 5-1/4" (13.3cm)  
Length: 13-1/4" (33.7cm)  
Width: 12-3/16" (30.9cm)  
Ceiling opening: 4" (10.2cm)

Height: 5-1/2" (14.0cm)  
Length: 10-1/8" (25.7cm)  
Width: 5-3/4" (14.6cm)  
Ceiling opening: 4-1/4" (10.8cm)  
Ceiling cutout template: 4.01"



## Specifications

---

### 301

---

**INTENDED USE:**

For use with housings L3 and L3R.

**INSTALLATION**

Socket to trim interface. Retaining clips pull and snap onto top of reflector to hold trim inside housing.

**LISTINGS:**

UL Listed to US and Canadian safety standards. Damp location listed. Pull on clip Patent No. (US) 5707143, (Canada) 2193902.

**WARRANTY:**

1-year limited warranty. Complete warranty terms located at:  
[www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

**Note:** Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

### 3BIW

---

**INTENDED USE:**

For use with housings L3 and L3R.

**INSTALLATION**

Socket to trim interface. Retaining clips pull and snap onto top of reflector to hold trim inside housing.

**LISTINGS:**

UL Listed to US and Canadian safety standards. Damp location listed. Pull on clip Patent No. (US) 5707143, (Canada) 2193902.

**WARRANTY:**

1-year limited warranty. Complete warranty terms located at:  
[www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

**Note:** Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

## Dimensions

---

All dimensions are inches (centimeters) unless otherwise indicated.

Height: 4-3/4" (12.1cm)

Lamp Opening: 3-1/2" (8.9cm)

Diameter: 4-7/8" (12.4cm)

Height: 4-3/4" (12.1cm)

Lamp Opening: 3-1/2" (8.9cm)

Diameter: 4-7/8" (12.4cm)



## Specifications

---

### 3E1

---

**INTENDED USE:**

For use with housings L3 and L3R.

**INSTALLATION**

Socket to trim interface. Retaining clips installed at factory to top of reflector to hold trim inside housing.

**LISTINGS:**

UL Listed to US and Canadian safety standards. Damp location listed. Pull on clip Patent No. (US) 5707143, (Canada) 2193902.

**WARRANTY:**

1-year limited warranty. Complete warranty terms located at:  
[www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

**Note:** Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

### 3H2O

---

**INTENDED USE:**

For use with housings L3 and L3R.

**INSTALLATION**

Socket to trim interface. Retaining clips pull and snap onto top of reflector to hold trim inside housing.

**LISTINGS:**

UL Listed to US and Canadian safety standards. Wet location listed when used with Sylvania outdoor rated 75W PAR30 short neck safety lamp. Reflector Patent No. (US) 6116750. Pull on clip Patent No. (US) 5707143, (Canada) 2193902.

**WARRANTY:**

1-year limited warranty. Complete warranty terms located at:  
[www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

**Note:** Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

## Dimensions

---

All dimensions are inches (centimeters) unless otherwise indicated.

Height: 4" (10.2cm)  
Lamp Opening: 3-1/2" (8.9cm)  
Diameter: 4-7/8" (12.4cm)

Height: 3" (7.6cm)  
Lamp Opening: 4" (10.2cm)  
Diameter: 5-1/4" (13.3cm)