



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30222 Set-Screw Conn, Model 22, 20-10 Awg, 100/Box

Ideal

Catalog Number	30222
Manufacturer	Ideal
Description	Ideal, Wire Connector, Set-Screw, Size: 11/16 In Width X 1-1/64 In Height, Number Of Conductors: 1 to 6, Wire Size: 20 - 10 Awg, Material: Brass, Flame-Retardant Polypropylene Shell, Color: Brass Connector, Black Shell, Voltage Rating: 600 V, Temperature Rating: 150 , 302 Deg C, Deg F, Model: 22, Width: 11/16 In, Height: 115625 In
Weight per unit	0.0200 (lbs/each)
Product Category	Utp Connectors

Features

Material	Brass/Flame-Retardant Polypropylene
Number of Conductors	1 to 6
Voltage Rating	600
Wire Size	20 - 10

Material, Color, and Finish

Color	Brass Connector, Black Shell
-------	------------------------------

Dimensions and Weight

Size	11/16 IN Width X 1-1/64 IN Height
------	-----------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	SET-SCREW CONN, MODEL 22, 20-10 AWG, 100/BOX
extra long description	IDEAL 30-222 SET SCREW 22 CONN(BOX
Features	Set screw wire connectors from IDEAL ensure a vibration-resistant splice, perfect for applications near motors or other vibration. The solid brass sleeve inserts come in three sizes, allowing wire ranges 22 AWG - 10 AWG. Each package contains plastic caps, allowing for insulation of the splice after installation, as well as a set screw holder to allow for ease of installation.
Long Description	IDEAL, Wire Connector, Set-Screw, Size: 11/16 IN Width X 1-1/64 IN Height, Number Of Conductors: 1 to 6, Wire Size: 20 - 10 AWG, Material: Brass, Flame-retardant polypropylene shell, Color: Brass Connector, Black Shell, Voltage Rating: 600 V, Temperature Rating: 150 , 302 DEG C, DEG F, Model: 22, Width: 11/16 IN, Height: 115625 IN
Product Type	Set Screw 22 Conn(Box Of 100)
Special Features	Features: Eliminates Need For Restripping Wire Each Time Connection Is Disturbed; Solid Brass Sleeves ;Set-Screw Easily And Securely Applies Maximum Compression To Conductors To Ensure A Vibration-Resistant Splice; Permits Fast Visual Inspection Of Splice; Tough, Flame-Retardant Shell Rated At 150°C (302°F); UI Listed To 486C And Csa Certified To C22.2; Model: 22; Width: 11/16 IN; Height: 115625 IN

Manufacturer Information

Brand	Ideal
GTIN	00783250302222
Manufacturers Part Number	30-222
UPC	783250302222

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Set-Screw

Packaging

Carton	100
Weight Per each	0.02

Uses, Certifications, and Standards

standard	CSA C22.2, 486C UL Listed
Temperature Rating	150 , 302