

Eaton 302410-12

Catalog Number: 302410-12

Eaton B-Line series wall mounted panel enclosure, 30" height, 10" length, 24" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series type 12 panel enclosures	302410-12
	UPC
	782051803402
Product Length/Depth	Product Height
10 in	30 in
Product Width	Product Weight
24 in	58.4 lb
Certifications	
UL 508A	
CSA C22.2.	
NEMA	

Material/finish

Material

Carbon steel

Wall thickness

14 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Medium single door

Model

12 enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

External mounting feet

Locking provisions

Padlock provision

Closure type

Hinged

Special features

Plated door clamps

Standards

NEMA Rating

12

Country of origin

US

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 302410-12](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)