

Eaton 302412-4XS

Catalog Number: 302412-4XS

Eaton B-Line series wall mounted panel enclosure, 30" height, 12" length, 24" width, NEMA 4X, Hinged cover, 4XS enclosure, Wall mount, Medium single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	302412-4XS
	UPC
	782051870022
Product Length/Depth	Product Height
12 in	30 in
Product Width	Product Weight
24 in	66.8 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

defaultTaxonomyAttributeLabel

Country of origin

US

Special features

Stainless door clamps

Style

Medium single door

Finish color

#4 brushed

Color

Gray

NEMA Rating

4X

Cover type

Hinged

Wall thickness

14 gauge

Material

304 stainless steel

Model

4XS enclosure

Mounting method

Wall

Closure type

Hinged

Locking provisions

Padlock provision

Mounting hole details

External mounting feet

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 302412-4XS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)