

Eaton 302412-SDSS4

Catalog Number: 302412-SDSS4

Eaton B-Line series wall mounted panel enclosure,30" height,12" length,24" width,NEMA 4X,Hinged cover,SDSS4 enclosure,Wall mount,Medium single door,Thru holes,opt. external mounting feet,304 stainless steel,Seamless poured in-place gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	302412-SDSS4
	UPC
	782051093698

Product Length/Depth	Product Height
12 in	30 in

Product Width	Product Weight
24 in	60.9 lb

Certifications

UL 50
CSA C22.2.
NEMA

Product specifications

Special features

Stainless 1/4 turn latches

Closure type

Hinged

Finish color

#4 brushed

Color

Gray

Wall thickness

14 gauge, 14 gauge

Material

304 stainless steel

Mounting method

Wall

Country of origin

US

Cover type

Hinged

Mounting hole details

Thru holes, optional external mounting feet

NEMA Rating

4X

Model

SDSS4 enclosure

Style

Medium single door

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 302412-SDSS4](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)