



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30244J Twister Pro Wire Conn, 344 Red/Tan, 250/Jar

Ideal

Catalog Number	30244J
Manufacturer	Ideal
Description	Ideal, Wire Connector, Twister Pro, Conductor Range: 22 - 8 Awg, 2/18 Awg Min, 4/10 Awg Max, Number Of Conductors: 2 to 4, Material: Flame-Retardant Polypropylene, Color: Red/Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 Deg F), Wire Type: Cu/Cu, Model Number: 344
Weight per unit	2.1 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-Retardant Polypropylene
Number of Conductors	2 to 4
Voltage Rating	600
Wire Type	Cu/Cu

Material, Color, and Finish

Color	Red/Tan
-------	---------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	TWISTER PRO WIRE CONN, 344 RED/TAN, 250/JAR
extra long description	IDEAL 30-244J TWISTER PRO 344 RED T
Features	Twister Wire Connectors have earned a solid reputation as the most technically advanced wire connector available. These superior wire connectors are designed from top to bottom with features to provide more comfort and less fatigue to professional electricians. With swept wings and an expanding, live-action spring, the Twister supports a wide range of common wiring configurations with comfort and ease, even on the toughest combinations like solid-to-stranded. The copolymer shell expands for smooth, progres
Long Description	IDEAL, Wire Connector, Twister PRO, Conductor Range: 22 - 8 AWG, 2/18 AWG Min, 4/10 AWG MAX, Number Of Conductors: 2 to 4, Material: Flame-retardant Polypropelene, Color: Red/Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F), Wire Type: Cu/Cu, Model Number: 344
Product Type	Twister Pro 344 Red Tan, 250 JR
Special Features	Features: The Widest Red/Tan Wire Range In The Industry; Min. 2 #18 To Max. 4 #10; Suregrip Overmolding Provides Better Grip For Improved Leverage And More Torque; Comfortable Swept Wings Designed To Help Reduce Hand Fatigue; Expanding Square-Wire Spring Provides A Secure Connection Every Time; Better Grip And More Leverage For Faster Connections With Less Effort; Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 Degree C (221 Degree F); UL Listed To 486C And CSA Certified To C22.2 #188; Comply With Feder

Manufacturer Information

Brand	Ideal
GTIN	00783250561384
Manufacturers Part Number	30-244J
sub brand	Twister® PRO
UPC	783250561384

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	--

Packaging

Carton	250
Package	1500
Weight Per each	2.125



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS