



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

303184 STRND GRND Tail-#10 Fork/#10 Ring/GRD SCRW, 25/Bag

Ideal

Catalog Number	303184
Manufacturer	Ideal
Description	Grounding Tail, Screw Terminal, Green, 0.02 LB/Ea
Weight per unit	0.0240 (lbs/each)
Product Category	Miniature/Appliance WRG Dev

Features

connection	#10 Fork And #10 Ring And Ground Screw
Wire Size	12
Wire Type	STRANDED

Descriptions

Description	STRND GRND TAIL-#10 FORK/#10 RING/GRD SCRW, 25/BAG
extra long description	IDEAL 30-3184 JUMPER W RING, SCREW
Special Features	Stranded pigtail lead wires are convenient for device grounding applications; Grounding screw offers a unique thread-forming, hole-finding feature plus combination 5/16 IN hex, #2 Phillips, 1/4 IN slotted and #2 Robertson head; Ultra-flexible lead wire tucks easily into box; Heavy-duty fork terminal attaches easily to grounding screw; Reduces time required for device bonding; Custom tails available

Manufacturer Information

Brand	Ideal
GTIN	00783250454525
UPC	783250454525

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Grounding Tail

Availability

minimum qty	25
-------------	----

Packaging

Carton	25
Package	250
Weight Per each	0.024

Uses, Certifications, and Standards

Application	For Device Grounding Applications
standard	C/US UL Listed, Ensures Compliance With NEC Standards, RoHS Compliant