



30382J Powerplug Disconnect, Model 102, 2-Wire, 75/Jar

Ideal

Catalog Number	30382J
Manufacturer	Ideal
Description	Disconnect Terminal, #12 Awg Conductor Size, Insulated, Nylon Insulation Material, Copper Alloy (Contacts) Conductor Material, Orange Insulation Color, 600 V Ac, 0.01 LB
Weight per unit	N/A
Product Category	Small Terminals & Connectors

Features

amperage rating	6
Material	Nylon Housing, Copper Alloy Contacts
Wire Size	12 - 18 AWG Solid, 12 - 14 AWG Stranded, 12 - 14, 16, 18 AWG Stranded Tin-Bonded

Material, Color, and Finish

Color	Orange
-------	--------

Descriptions

Description	POWERPLUG DISCONNECT, MODEL 102, 2-WIRE, 75/JAR
extra long description	IDEAL 30-382J POWERPLUG DISC 102, 7
Features	Patented push-in technology quickly locks wires in placeAllows for safe disconnect of hot and neutral ballast wiringBoth halves are touch-safe? per UL 2459Push-in technology results in quicker connections, saving time and increasing productivityFits through 1/2 in. knockoutKits available for all lighting installation and maintenance needsThe PowerPlug features patented IDEAL push-in technology that quickly locks wires in place. It helps reduce electrical shock hazard during ballast replacement by safely di

Manufacturer Information

Brand	Ideal
GTIN	00783250656844
UPC	783250656844

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	2-Wire Standard Version

Availability

minimum qty	75
-------------	----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

800 Old Boston Road
75501-0000, TX Texarkana
Phone: 903-223-6400
Fax: 903-223-6700

Packaging

Carton	75
Package	450
Weight Per each	0

Uses, Certifications, and Standards

standard	CSA, UL Listed, RoHS
----------	----------------------